



Metric



Metric table

Dimensions in: millimeters / inches

d ₁	Length l					a min.	b	d ₂	d ₃	d ₄	d ₅	d ₆	h ₁	h ₂	m	A/F	t min.
	300	400	500	600	1000												
30	300	400	500	600	1000	70	27.5	M 10	46	46.6	42	8	60	84	13.5	5	20
1.18	11.81	15.75	19.69	23.62	39.37	2.76	1.08		1.81	1.83	1.65	0.31	2.36	3.31	0.53		0.79
40	400	600	800	1000		70	30	M 12	56	56.8	50	8	70	99	18.5	5	25
1.57	15.75	23.62	31.50			2.76	1.18		2.20	2.24	1.97	0.31	2.76	3.90	0.73		0.98

Specification

Handle tube	Stainless steel AISI 304 Ground, matte finish (Ra < 0.8 µm)	NI MT
Handle legs	Stainless steel AISI 304 Matte finish (Ra < 0.8 µm)	
Sealing ring / Wiper	TPU	T
Clamping wedge	Brass	
Set screw	Stainless steel	
RoHS		

Tubular handles GN 3330 comply with the DGVU testing principles and are designed for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the non-concave geometry prevent adherence of dirt and facilitate cleaning. The movable handle legs are loosely enclosed for fastening to the handle tube using the integrated clamping wedge during installation. The position of the handle legs can be adjusted as required, but must not be less than the minimum distance a, as the tubes may be undersized in the edge area. For large lengths or loads, additional movable handle legs can be added. These are available under standard part number GN 3331.

Technical Information

Product Family Hygienic Design	Page QVX
Plastic Characteristics	Page QVX
Stainless Steel Characteristics	Page QVX

Accessory

GN 1580 Hex Head Screws	Page QVX
GN 1581 Hex Head Screws	Page QVX
GN 3331 Straight Handle Legs	Page QVX

How to order

1	Material
2	Handle diameter d ₁
3	Length l
4	Finish
5	Sealing ring material

GN 3330-NI-40-1000-MT-T

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

