


Metric



**SS** Stainless Steel

**3 Type**

- D** With plain stud
- E** With threaded stud

Metric table



Dimensions in: millimeters / inches

$d_1$	$d_2$ h8 Type D ST	$d_3$ Type E			$d_4$ h13	$l_1 \approx$	$l_2$	$l_3$	A/F Internal hex
		ST	A4	KT					
16 0.63	7 0.276	M 6	M 6	-	10 0.394	50 1.97	11 0.43	7 0.28	3
20 0.79	8 0.315	M 8	M 8	M 8	13 0.512	64 2.52	13 0.51	8 0.31	4
25 0.98	10 0.394	M 10	M 10	M 10	16 0.630	80 3.15	14 0.55	10 0.39	5
32 1.26	13 0.512	M 12	-	M 12	20 0.787	100 3.94	21 0.83	13 0.51	6
36 1.42	16 0.630	M 16	-	-	22 0.866	112 4.41	26 1.02	14 0.55	8

**Specification**



<b>Steel</b> , zinc plated, blue passivated finish	<b>ST</b>
<b>Stainless steel</b> AISI 316L	<b>A4</b>
<b>Plastic</b> , Polyamid (PA)	<b>KT</b>
<ul style="list-style-type: none"> <li>• Operating temperature up to 213 °F (100 °C)</li> <li>• Black, matte finish</li> <li>• Threaded stud</li> <li>• Steel, blackened finish</li> </ul>	

RoHS

Fixed handles DIN 39 are used in applications where a positive non-revolving grip is required.

For hygienic reasons, a hexagonal recess is not used in type A4.

**Technical Information**

ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

**DIN 39-ST-25-E**

<b>1</b>	Material
<b>2</b>	Handle diameter $d_1$
<b>3</b>	Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

