


**Application example**



- 3 Type**
- B** Smooth contact face
  - K** Spherical contact face
  - R** Serrated contact face

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> h Type B: ±0.01 Type K / R: ±0.1	<b>2</b> d <sub>1</sub>	d <sub>2</sub> Type B / R	Length l	A/F	e Width across corners
10 0.39	M 8	17 0.67	10 0.39	17 0.67	19.4 0.76
10 0.39	M 10	19 0.75	12 0.47	19 0.75	21.9 0.86
10 0.39	M 12	22 0.87	14 0.55	22 0.87	25.2 0.99
15 0.59	M 10	19 0.75	12 0.47	19 0.75	21.9 0.86
15 0.59	M 12	22 0.87	14 0.55	22 0.87	25.2 0.99
15 0.59	M 16	30 1.18	19 0.75	30 1.18	34.2 1.35
20 0.79	M 16	30 1.18	19 0.75	30 1.18	34.2 1.35

**Specification**

- Steel
  - Case-hardened
  - Blackened finish
- RoHS compliant

**Information**

GN 409.1 positioning elements with threaded stem are designed for use as supports, stops and thrust blocks.

see also...

- Locating / Seating Pins DIN 6321 → page 1178
- Press-Fit Drill Bushings DIN 172 / DIN 179 → page 1172

<b>How to order</b> <b>GN 409.1-15-M10-B</b>	<b>1</b>	Height h
	<b>2</b>	Thread d <sub>1</sub>
	<b>3</b>	Type

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

