



Metric table



Dimensions in: millimeters - inches

b h6	d ₁	d ₂	h	Length l	t	For DIN 84 / DIN 912 screws with thread size
10 0.39	4.5 0.18	8 0.31	8 0.31	20 0.79	4.3 0.17	M4 x 10
12 0.47	5.5 0.22	10 0.39	8 0.31	20 0.79	5.3 0.21	M5 x 12
14 0.55	6.6 0.26	11 0.43	10 0.39	22 0.87	6.3 0.25	M6 x 16
16 0.63	6.6 0.26	11 0.43	10 0.39	22 0.87	6.3 0.25	M6 x 16
18 0.71	6.6 0.26	11 0.43	10 0.39	22 0.87	6.3 0.25	M6 x 16
20 0.79	6.6 0.26	11 0.43	10 0.39	22 0.87	6.3 0.25	M6 x 16
22 0.87	6.6 0.26	11 0.43	12 0.47	32 1.26	6.3 0.25	M6 x 16

Specification

- Steel
 - Case-hardened
 - Blackened finish
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

Information

GN 230 tenon nuts are used for aligning and positioning of jigs and fixtures on machining tables with DIN 650 T-slots.

For this purpose they are screwed into the aligning slots of the jig or fixture.

How to order	1	Width b
GN 230-12		

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

