


Metric



Metric table

Dimensions in: millimeters / inches

d₁	d₂		d₃ ≈	h	t min.
20 0.79	M 5	M 6	12 0.47	30 1.18	18 0.71
25 0.98	M 6	M 8	15 0.59	38 1.50	18 0.71
30 1.18	M 8	M 10	18 0.71	46 1.81	18 0.71
35 1.38	M 10	M 12	21 0.83	53 2.09	21 0.83

Specification

Plastic, Phenolic (PF)

- Operating temperature up to 230 °F (110 °C)
- Black, shiny finish

RoHS

Tapered knobs GN 419 are used as switching and operating elements. They are actuated by pushing or pulling in the axial direction with two fingers. Their shape also makes them easy to grip with the entire hand, meaning that higher operating forces can be transmitted.

The tapered knobs of phenolic resin have good resistance to chemical influences.

Technical Information

Plastic Characteristics

Page

QVX

How to order

GN 419-25-M8

1 Handle diameter **d₁**

2 Thread **d₂**