



SS Stainless Steel

- 3 Identification no.**
2 With 3 stainless steel socket cap screws DIN 912

Metric table

1 2

Dimensions in: millimeters - inches

d ₁ Bore	d ₂ Bore						b Swivel width	k ₁	k ₂	l ₁	l ₂	l ₃	m ₁	m ₂	z ₁ Screw locations for screw size	z ₂ Screw location for screw size	Accessory Recommended lever GN 911.3			
B 12	B 12	B 14	B 15	B 16	B 18	B 20	25 0.98	31.5 1.24	25 0.98	100 3.94	34.5 1.36	25 0.98	29.5 1.16	48.5 1.91	M6-20	M6-20	-	-	45 1.77	63 2.48
B 14	B 12	B 14	B 15	B 16	B 18	B 20	25 0.98	31.5 1.24	25 0.98	100 3.94	34.5 1.36	25 0.98	29.5 1.16	48.5 1.91	M6-20	M6-20	-	-	45 1.77	63 2.48
B 15	B 12	B 14	B 15	B 16	B 18	B 20	25 0.98	31.5 1.24	25 0.98	100 3.94	34.5 1.36	25 0.98	29.5 1.16	48.5 1.91	M6-20	M6-20	-	-	45 1.77	63 2.48
B 16	B 12	B 14	B 15	B 16	B 18	B 20	25 0.98	31.5 1.24	25 0.98	100 3.94	34.5 1.36	25 0.98	29.5 1.16	48.5 1.91	M6-20	M6-20	-	-	45 1.77	63 2.48
B 18	B 12	B 14	B 15	B 16	B 18	B 20	25 0.98	31.5 1.24	25 0.98	100 3.94	34.5 1.36	25 0.98	29.5 1.16	48.5 1.91	M6-20	M6-20	63 2.48	-	45 1.77	63 2.48
B 20	B 12	B 14	B 15	B 16	B 18	B 20	25 0.98	31.5 1.24	25 0.98	100 3.94	34.5 1.36	25 0.98	29.5 1.16	48.5 1.91	M6-20	M6-20	45 1.77	63 2.48	45 1.77	63 2.48

Specification

4

- Body
Stainless steel AISI CF-8
Matte shot-blasted finish
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page 2143
- [RoHS compliant](#)

NI

Accessory

- Adjustable levers GN 911.3 → page 1811

Information

GN 287 swivel clamp connector joints are an assembly of GN 275 and GN 277 swivel clamp connectors. The clamping bores are mechanically machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw locations z₁, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911.3 adjustable levers listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → page 1836
- *Rods / Tubes GN 480.1* → page 1838
- *Swivel Clamp Connectors GN 275* → www.jwwinco.com
- *Swivel Clamp Connectors GN 277* → www.jwwinco.com

How to order

GN 287-B16-B15-2-NI

1	Bore d ₁
2	Bore d ₂
3	Identification no.
4	Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10