




Metric table

1

2

Dimensions in: millimeters / inches

d ₁	Length l ±0.5			d ₂ H12	h	r	t
8 0.31	64 2.52	88 3.46	100 3.94	3 0.118	35 1.38	10 0.39	5 0.20
10 0.39	100 3.94	125 4.92	160 6.30	3 0.118	43 1.69	12 0.47	5 0.20
12 0.47	125 4.92	160 6.30	200 7.87	4 0.157	51 2.01	14 0.55	6 0.24
16 0.63	125 4.92	160 6.30	200 7.87	4 0.157	59 2.32	18 0.71	6 0.24
20 0.79	200 7.87	250 9.84	-	5 0.197	68 2.68	22 0.87	8 0.31

Specification	3
Steel	ST
Plain finish	
Stainless steel AISI 304	NI
Matte shot-blasted finish	
RoHS	

Technical Information	Page
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

Cabinet U-handles GN 425.3 have no thread and are designed for applications that require the handle to be welded or for applications that require special threads, holes, etc. for mounting.

If required, the holes d₂ serve for inserting dowel pins or location pins that position the cabinet U-handle in place via the alignment holes in the opposing part and thus easily fix the handle during the welding process.

see also...	Page
GN 426.3 Cabinet U-Handles (Steel, Weldable)	QVX
GN 425 Cabinet U-Handles (Steel / Aluminum / Stainless Steel)	QVX
GN 426 Cabinet U-Handles (Aluminum)	QVX

How to order	1	Handle diameter d ₁
	2	Length l
	3	Material
GN 425.3-12-160-NI		