





Metric



**elesa**  
Original design MMT.



Metric table

| Dimensions in: millimeters / inches   |                                            |                |            |                |                |                |                |                |                |            |
|---------------------------------------|--------------------------------------------|----------------|------------|----------------|----------------|----------------|----------------|----------------|----------------|------------|
| <div>1</div> <div>d<sub>1</sub></div> | <div>2</div> <div>l<sub>1</sub> ±0.5</div> | l <sub>2</sub> | b          | d <sub>2</sub> | d <sub>3</sub> | h <sub>1</sub> | h <sub>2</sub> | h <sub>3</sub> | h <sub>4</sub> | t min.     |
| 10<br>0.39                            | 120<br>4.72                                | 94<br>3.70     | 16<br>0.63 | M 5            | 18<br>0.71     | 53<br>2.09     | 43<br>1.69     | 8<br>0.31      | 24<br>0.94     | 12<br>0.47 |
| 10<br>0.39                            | 180<br>7.09                                | 94<br>3.70     | 16<br>0.63 | M 5            | 18<br>0.71     | 56<br>2.20     | 43<br>1.69     | 8<br>0.31      | 24<br>0.94     | 12<br>0.47 |

Specification

Handle

Steel  
Matte chrome-plated finish

Grip

Plastic, Polyamide PA  
• Glass fiber reinforced  
• Operating temperature  
-22 °F to 302 °F (-30 °C to +150 °C)  
• Black, matte finish

RoHS

Cabinet U-handles EN 425.7 made of steel feature a plastic grip which, owing to its insulating properties, allows it to be used under high surface temperatures.

The above temperature distribution curve has been measured at a surface temperature of 392 °F (200 °C) and a room temperature of 73 °F (23 °C).

see also...

GN 425 Cabinet U-Handles (Steel) Page QVX

Technical Information

Plastic Characteristics QVX