



**Specification**



- Lever body  
Zinc die-cast
- Powder coated
  - Black, RAL 9005, textured finish ● **SW**
  - Orange, RAL 2004, textured finish ● **OS**
  - Red, RAL 3000, textured finish ● **RS**
  - Silver, RAL 9006, textured finish ● **SR**
- Push button
  - Plastic
  - Black, RAL 9005 ● **S**
  - Orange, RAL 2004 ● **O**
  - Gray, RAL 7035 ● **G**
- Insert  
Steel, blackened finish
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

**Information**

GN 304 adjustable levers with push button have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The push button is a design element and allows for effortless release action. However, this design is limited to applications that do not require the lever to be disassembled.

see also...

- Straight Adjustable Levers WN 304 (Nylon Plastic, with Push Button, with Steel Insert) → page 472
- Straight Adjustable Levers GN 302 (Zinc Die-Cast, with Steel Insert) → page 452
- Straight Adjustable Levers WN 302 (Nylon Plastic, with Steel Insert) → page 458

**On request**

- Special bores and threads

How to order (Inch)	1 Lever length $l_1$
1 2 3 4	2 Bore $d_2$ (Thread $d_1$ )
<b>GN 304-30-B1/4-OS-O</b>	3 Lever color
	4 Push button color
How to order (Metric)	1 Lever length $l_1$
1 2 3 4	2 Thread $d_1$ (Bore $d_2$ )
<b>GN 304-63-M8-RS-S</b>	3 Lever color
	4 Push button color

**Inch table**

Dimensions in: inches - *millimeters*

l <sub>1</sub>	d <sub>1</sub> Thread			d <sub>2</sub> +0.001 Bore		d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke	t min.
1.18 30	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	0.35 9
1.77 45	10 x 32	10 x 24	1/4 x 20	B 1/4	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	B 1/4	B 5/16	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	3/8 x 24	B 5/16	B 3/8	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4	0.55 14

**Metric table**

Dimensions in: millimeters - *inches*

l <sub>1</sub>	d <sub>1</sub> Thread			d <sub>2</sub> H7 Bore		d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub> Stroke	t min.
30 1.18	M 3	-	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	7 0.28
30 1.18	M 4	M 5	M 6	B 5	B 6	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	B 5	B 6	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	B 6	B 8	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16	11 0.43
78 3.07	M 8	M 10	-	B 8	B 10	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16	14 0.55

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

