



SS Stainless Steel

4 Type

KS With plastic cap, gliding
KR With rubber cap, non-skid

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	l ₁		l ₂ ≈	l ₃ ≈	l ₄		A/F	Static load
						Type KS	Type KR		
29 1.14	M 6	30 1.18	45 1.77	8 0.31	5 0.20	1 0.04	0.4 0.02	3	6 kN 1349 lbf
29 1.14	M 8	35 1.38	55 2.17	8 0.31	5 0.20	1 0.04	0.4 0.02	4	13 kN 2923 lbf
36 1.42	M 8	40 1.57	65 2.56	9 0.35	6 0.24	1 0.04	0.5 0.02	4	13 kN 2923 lbf
36 1.42	M 10	45 1.77	70 2.76	9 0.35	6 0.24	1 0.04	0.5 0.02	5	18 kN 4047 lbf

Specification

- Leveling foot
Steel **ST**
- Property class 5.8
- Zinc plated, blue passivated finish
Hex nut ISO 4035
Steel, zinc plated, blue passivated finish
- Leveling foot
Stainless steel AISI 303 **NI**
Hex nut ISO 4035
Stainless steel AISI 304
- Type **KS**
Plastic cap
Technopolymer (Polyacetal POM)
White, RAL 9001, natural color
- Type **KR**
Rubber cap
Elastomer (TPE) ≈ 73 shore A
Black
- Strength Values of Screws → page 2127
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 339 leveling feet are used for applications where no jointed link is required between the base and the threaded stud.
They are characterized by a low overall height.
The gliding / non-skid cap is firmly embedded in the base.
see also...
• *Disks with Cover Cap GN 338* → www.jwwinco.com
• *Threaded Tube Ends EN 448* → page 1576 / 1578
• *Threaded Mounting Plates GN 349* → www.jwwinco.com
• *Ball Jointed Leveling Feet GN 638* → page 1492

How to order	
1	Base diameter d ₁
2	Thread d ₂
3	Stud length l ₁
4	Type
5	Material

GN 339-36-M10-45-KR-ST

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10