



SS Stainless Steel

4 Type

A Without rubber pad  
G With rubber pad

### Specification

- Base  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 212 °F (100 °C)  
- Black, matte finish
- Tapped socket / threaded stud  
Stainless steel AISI 303
- Hex nut ISO 4032  
Stainless steel AISI 304
- Rubber pad  
Perbunan® (NBR) 70 shore A  
Black
- [Plastic Characteristics](#) → page 2135
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

### On request

- ESD version  
(conductive plastic to avoid static charge;  
see also GN 343.5 / GN 343.6, type KSE or KRE)

### Information

GN 343.7 and GN 343.8 leveling feet can bear high static loads through the use of a high quality plastic material, coupled with a design that distributes the load over a larger area.

Exceeding the static values listed in the table can result in damage to the plastic base.

The values in the table were determined by a series of tests, where a limited number of leveling feet were subjected to a vertical static load, in relation to the foot, for a limited time.

Depending on the application and load case, however, a safety factor must be considered so that the permissible load capacity is below the value given in the table.

These leveling feet are supplied assembled but can be disassembled.

see also...

- [Leveling Feet GN 343.1 / GN 343.2 \(Steel\)](#) → page 1466
- [Leveling Feet GN 343.3 / GN 343.4 \(Plastic Base, Steel Tapped Socket / Threaded Stud\)](#) → page 1468
- [Leveling Feet GN 343.5 / GN 343.6 \(Stainless Steel\)](#) → page 1470
- [Vibration Damping Leveling Feet GN 342.1 / GN 342.2](#) → [www.jwwinco.com](http://www.jwwinco.com)
- [Threaded Tube Ends EN 448](#) → page 1578 / 1578

How to order (Tapped socket type)	1 Base diameter $d_1$
1 2 4 <b>GN 343.7-32-M10-G</b>	2 Thread $d_2$
	4 Type
How to order (Threaded stud type)	1 Base diameter $d_1$
1 2 3 4 <b>GN 343.8-60-M16-125-A</b>	2 Thread $d_2$
	3 Stud length $l_1$
	4 Type

**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>		l <sub>1</sub>			l <sub>2</sub>	l <sub>3</sub>	A/F	t min.	Static load (See information)	
	GN 343.7	GN 343.8								Type A	Type G
25 0.98	M 6	M 6	40 1.57	50 1.97	63 2.48	18.5 0.73	4 0.16	12 0.47	9 0.35	5 kN 1124 lbf	1 kN 225 lbf
25 0.98	M 8	M 8	40 1.57	50 1.97	63 2.48	18.5 0.73	4 0.16	12 0.47	9 0.35	5 kN 1124 lbf	1 kN 225 lbf
25 0.98	-	M 10	50 1.97	63 2.48	80 3.15	18.5 0.73	4 0.16	12 0.47	-	5 kN 1124 lbf	1 kN 225 lbf
32 1.26	M 8	M 8	40 1.57	50 1.97	63 2.48	22.5 0.89	5 0.20	12 0.47	9 0.35	7 kN 1574 lbf	2 kN 450 lbf
32 1.26	M 10	M 10	50 1.97	63 2.48	80 3.15	22.5 0.89	5 0.20	15 0.59	10.5 0.41	7 kN 1574 lbf	2 kN 450 lbf
32 1.26	-	M 12	63 2.48	80 3.15	100 3.94	22.5 0.89	5 0.20	15 0.59	-	7 kN 1574 lbf	2 kN 450 lbf
40 1.57	-	M 8	50 1.97	63 2.48	80 3.15	25.5 1.00	6 0.24	15 0.59	-	10 kN 2248 lbf	3 kN 674 lbf
40 1.57	M 10	M 10	50 1.97	63 2.48	80 3.15	25.5 1.00	6 0.24	15 0.59	10.5 0.41	10 kN 2248 lbf	3 kN 674 lbf
40 1.57	M 12	M 12	63 2.48	80 3.15	100 3.94	25.5 1.00	6 0.24	17 0.67	11.5 0.45	10 kN 2248 lbf	3 kN 674 lbf
50 1.97	-	M 8	50 1.97	63 2.48	80 3.15	27.5 1.08	7 0.28	15 0.59	-	10 kN 2248 lbf	4 kN 899 lbf
50 1.97	M 10	M 10	50 1.97	63 2.48	80 3.15	27.5 1.08	7 0.28	15 0.59	10.5 0.41	10 kN 2248 lbf	4 kN 899 lbf
50 1.97	M 12	M 12	63 2.48	80 3.15	100 3.94	27.5 1.08	7 0.28	17 0.67	11.5 0.45	10 kN 2248 lbf	4 kN 899 lbf
50 1.97	-	M 16	63 2.48	80 3.15	100 3.94	27.5 1.08	7 0.28	17 0.67	-	10 kN 2248 lbf	4 kN 899 lbf
60 2.36	-	M 10	50 1.97	63 2.48	80 3.15	27.5 1.08	7 0.28	17 0.67	-	14 kN 3147 lbf	6 kN 1349 lbf
60 2.36	M 12	M 12	63 2.48	80 3.15	100 3.94	35.5 1.40	8.5 0.33	17 0.67	11.5 0.45	14 kN 3147 lbf	6 kN 1349 lbf
60 2.36	M 16	M 16	80 3.15	100 3.94	125 4.92	35.5 1.40	8.5 0.33	24 0.94	16 0.63	14 kN 3147 lbf	6 kN 1349 lbf
60 2.36	-	M 20	98 3.86	138 5.43	158 6.22	35.5 1.40	8.5 0.33	24 0.94	-	14 kN 3147 lbf	6 kN 1349 lbf
60 2.36	-	M 24	98 3.86	138 5.43	158 6.22	35.5 1.40	8.5 0.33	24 0.94	-	14 kN 3147 lbf	6 kN 1349 lbf



3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

