



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₃ Thread	³ Length l	d ₄	h ₁	h ₂	t min.
1.73 43.9	5/16 x 18	1.00 25.4	0.67 17.0	0.94 23.9	0.39 9.9	0.51 13.0
2.13 54.1	3/8 x 16	1.25 31.8	0.79 20.1	1.18 30.0	0.49 12.4	0.71 18.0

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ H9 Bore	² d ₃ Thread	³ Length l	d ₄	h ₁	h ₂	t min.		
44 1.73	B 6	M 6	10 0.39	20 0.79	-	17 0.67	24 0.94	10 0.39	13 0.51
44 1.73	-	M 8	16 0.63	30 1.18	50 1.97	17 0.67	24 0.94	10 0.39	13 0.51
54 2.13	B 8	M 8	16 0.63	30 1.18	50 1.97	20 0.79	30 1.18	12.5 0.49	18 0.71
54 2.13	-	M 10	20 0.79	30 1.18	50 1.97	20 0.79	30 1.18	12.5 0.49	18 0.71

Specification

- Body
Plastic
Technopolymer (Polypropylene PP)
- Softline coating
Elastomer (TPE) 70 shore A
 - Chemically bonded with the plastic body
 - FDA compliant plastic granulate
 - Temperature resistant up to 176 °F (80 °C)
 - Black, matte finish
- Insert
Brass
- Threaded stud
Steel, zinc plated, blue passivated finish
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Additional thread sizes

Information

The Softline coating of EN 4534 knurled knobs makes them particularly ergonomic and easy to grip. The soft, slip-proof contact area improves the grip both in damp (hand perspiration) and in dry ambient conditions, as well as in the event of oily surfaces and in very high or very low temperatures. The use of knurled knobs is particularly recommended if frequent or strong tightening is required.

see also...

- Product Family Softline → page QVX
- Diamond Cut Knurled Knobs EN 534 (with Brass Tapped or Plain Blind Bore Insert) → page QVX
- Diamond Cut Knurled Knobs EN 534 (with Steel Threaded Stud) → page QVX

How to order (Brass insert)	¹ Handle diameter d ₁
EN 4534-54-B8	² Bore d ₂ (Thread d ₃)

How to order (Steel threaded stud)	¹ Handle diameter d ₁
EN 4534-1.73-5/16X18-1.00	² Thread d ₃
	³ Length l