



**Metric**



**elesa**  
Original design M.479

**2 Type**

- A** Mounting from the back
- B** Mounting from the operator's side

**Metric table**



Dimensions in: millimeters / inches

$l_1 \pm 0.5$	$d_1$ Type A	$d_2$ Type B	$b$	$h_1$	$h_2$	$l_2$	$l_3$	$s$	$t_1$	$t_2$
132 5.20	M 8	8.5 0.33	23 0.91	52.5 2.07	13 0.51	173 6.81	113 4.45	9 0.35	12 0.47	8.5 0.33

**Specification**



**Handle**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature  
-22 °F to 266 °F (-30 °C to +130 °C)
- Black-gray, shiny finish, similar to RAL 7021

**Tapped insert (Type A)**

Brass

**Cover cap**

- Plastic, Polyamide (PA)
- Black-gray, RAL 7021, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Yellow, RAL 1021, matte finish
- Blue, RAL 5024, matte finish
- Red, RAL 3000, matte finish
- Green, RAL 6017, matte finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

**On request**

- Various metric size fasteners and kit packaging

The cover caps of arch handles GN 365 for type A are mounted on the handle, but supplied loose for type B.

**Technical Information**

Technical Information	Page
Plastic Characteristics	QVX
Strength Values	QVX

**How to order**

**EN 365-132-A-DSG**

<b>1</b>	Length $l_1$
<b>2</b>	Type
<b>3</b>	Color of the cover cap