



Metric



3 Type

- F With fixed handle
- D With revolving handle

Metric table

Dimensions in: millimeters / inches

Length l	1 s H11		2 e min.		2 d1 H7 Bore	d2	h1	h2	h3 ≈	h4 ≈		Ø Handle
	Square		(Column 1)	(Column 2)						Type D	Type F	
63 2.48	V 10	-	13.1 0.52	-	-	20 0.79	20 0.79	11 0.43	32 1.26	54.5 2.15	50 1.97	16 0.63
80 3.15	V 10	V 12	13.1 0.52	16.1 0.63	B 8	24 0.94	24 0.94	13 0.51	38 1.50	61 2.40	56 2.20	18 0.71
100 3.94	V 12	V 14	16.1 0.63	18.1 0.71	B 10	28 1.10	28 1.10	13 0.51	48 1.89	67 2.64	64 2.52	20 0.79
125 4.92	V 14	V 17	18.1 0.71	22.2 0.87	B 10	34 1.34	34 1.34	14 0.55	55 2.17	76 2.99	72 2.83	22 0.87
160 6.30	V 17	V 19	22.2 0.87	25.2 0.99	B 14	38 1.50	38 1.50	14 0.55	65 2.56	83 3.27	80 3.15	25 0.98
200 7.87	V 19	V 22	25.2 0.99	28.2 1.11	B 17	44 1.73	44 1.73	21 0.83	78 3.07	96.5 3.80	90 3.54	28 1.10
250 9.84	V 22	V 24	28.2 1.11	32.2 1.27	B 17	48 1.89	48 1.89	21 0.83	90 3.54	105.5 4.15	100 3.94	32 1.26
315 12.40	V 24	V 27	32.2 1.27	36.2 1.43	B 20	54 2.13	54 2.13	26 1.02	105 4.13	117 4.61	112 4.41	36 1.42

Specification

Crank body

Cast iron (GGG)

- Powder coated
- Black, textured finish
- Contact face of hub machined

Fixed handle DIN 39 for Type F

Steel

Zinc plated, blue passivated finish

Revolving handle DIN 98 for Type D

Steel

Zinc plated, blue passivated finish

RoHS

On request

- Other modifications such as inch and special metric bores, squares, keyways, set screw holes, etc.

Off-set crank handles DIN 468 are available with steel hand pieces as standard. If plastic hand pieces are required, please specify when ordering.

see also...

DIN 469 Straight Crank Handles Page QVX

Technical Information

Cross Holes GN 110 QVX

Square Bores WN 79 QVX

ISO Fundamental Tolerances QVX

How to order

DIN 468-100-V14-F

- 1 Length l
- 2 Square s (Bore d1)
- 3 Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

