


Metric



Metric table

Dimensions in: millimeters / inches

b	d		l₁ ±0.5	a	h	l₂	l₃	l₄	t min.
36 1.42	M 6	M 8	200 7.87	24 0.94	57 2.24	236 9.29	164 6.46	290 11.42	15 0.59
36 1.42	M 6	M 8	250 9.84	24 0.94	57 2.24	286 11.26	214 8.43	340 13.39	15 0.59
36 1.42	M 6	M 8	300 11.81	24 0.94	57 2.24	336 13.23	264 10.39	390 15.35	15 0.59
36 1.42	M 6	M 8	400 15.75	24 0.94	57 2.24	436 17.17	364 14.33	490 19.29	15 0.59
36 1.42	M 6	M 8	500 19.69	24 0.94	57 2.24	536 21.10	464 18.27	590 23.23	15 0.59
36 1.42	M 6	M 8	600 23.62	24 0.94	57 2.24	636 25.04	564 22.20	690 27.17	15 0.59

Specification

Handle tube

Aluminum

- Powder coated
Black, RAL 9005, textured finish **● SW**
 - Anodized finish, natural color **● ELS**
 - Anodized finish, natural color **● ELG**
- Handle legs / Covers, black, matte finish
- Handle legs / Covers, black, matte finish
- Handle legs / Covers, light gray, matte finish

Handle legs / Covers

Plastic, Polyamide (PA)

- Glass fiber reinforced
- Operating temperature up to 212 °F (100 °C)

Tapped inserts

Steel, zinc plated

RoHS

On request

Special tube lengths other than listed

Unique to the design of the tubular handles GN 366 is that the tube and the handle legs are in the same elliptical profile.

see also...

GN 334 Oval Tubular Handles (Mounting from the Back) **Page QVX**

Technical Information

Load Capacity Information **QVX**

Plastic Characteristics **QVX**

How to order

1	Handle diameter b
2	Thread d
3	Length l₁
4	Finish

GN 366-36-M8-400-ELS

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

