



Inch | Metric



Inch table

Dimensions in: inches / millimeters

Length l	d ₁ H7 Bore	s H11 Square	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	h ₅ ≈	Ø Handle GN 598	
3.94 100	B 1/2	-	V 1/2	1.06 27	1.18 30	1.10 28	0.67 17	0.51 13	0.77 19.5	2.66 67.5	0.91 23
4.92 125	B 5/8	-	V 5/8	1.26 32	1.38 35	1.34 34	0.87 22	0.55 14	0.77 19.5	2.66 67.5	0.91 23
6.30 160	B 1/2	B 3/4	V 3/4	1.38 35	1.54 39	1.50 38	1.02 26	0.63 16	0.77 19.5	3.25 82.5	1.02 26

Metric table

Dimensions in: millimeters / inches

Length l	d ₁ H7 Bore	s H11 Square	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	h ₅ ≈	Ø Handle GN 598
100 3.94	B 12	V 12	27 1.06	30 1.18	28 1.10	17 0.67	13 0.51	19.5 0.77	67.5 2.66	23 0.91
125 4.92	B 14	V 14	32 1.26	35 1.38	34 1.34	22 0.87	14 0.55	19.5 0.77	67.5 2.66	23 0.91
160 6.30	B 17	V 17	35 1.38	39 1.54	38 1.50	26 1.02	16 0.63	19.5 0.77	82.5 3.25	26 1.02

Specification

Crank body

- Aluminum
- Powder coated
- Black, textured finish
- Contact face of hub machined

Retractable handle GN 598.3

- Plastic, phenolic resin (PF)
- Black, shiny finish
- Retractable mechanism
- Steel, blackened finish

RoHS

On request

- Other modifications such as special inch and metric bores, squares, keyways, set screw holes, etc.
- With retractable handles EN 598.5 (Stainless steel retractable mechanism)

Crank handles GN 471.3 are mainly used for applications where the hand piece must not protrude.

In the operating position, the hand piece is firmly locked.

By pulling the hand piece in the axial direction out of its locating cone, it can be folded back into place.

The spring holds the hand piece firmly in both positions.

see also...

EN 570.3 Crank Handles (Plastic, with Blind Bore) Page QVX

Technical Information

Cross Holes GN 110 QVX

Square Bores WN 79 QVX

ISO Fundamental Tolerances QVX

How to order (Inch)

GN 471.3-100-B1/2

1	Length l
2	Bore d ₁ (Square s)

How to order (Metric)

GN 471.3-125-V12

1	Length l
2	Square s (Bore d ₁)

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4