



Metric



SS Stainless Steel

IF product design award

GERMAN DESIGN AWARD

Metric table

¹ d ₁	² d ₂ Thread	² d ₃ H9 Bore	b	d ₄	h ₁	h ₂ ≈	t min.
63 2.48	M 6	B 6	7 0.28	16 0.63	41 1.61	12 0.47	12 0.47
63 2.48	M 8	B 8	7 0.28	16 0.63	41 1.61	12 0.47	16 0.63
80 3.15	M 8	B 8	9 0.35	21 0.83	52 2.05	15 0.59	16 0.63
80 3.15	M 10	B 10	9 0.35	21 0.83	52 2.05	15 0.59	20 0.79
100 3.94	M 10	B 10	11 0.43	25 0.98	65 2.56	19 0.75	20 0.79
100 3.94	M 12	B 12	11 0.43	25 0.98	65 2.56	19 0.75	24 0.94

Dimensions in: millimeters / inches

Specification

Stainless steel precision casting AISI 316

- Matte shot-blasted finish
- Polished finish

MT
PL

RoHS

T-handles GN 5063 are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the materials used.

see also...

	Page
EN 563 T-Handles (Plastic)	QVX
EN 563.1 T-Handles (Plastic)	QVX
GN 563.2 T-Handles (Aluminum)	QVX
GN 8340 Wing Nuts (Stainless Steel)	QVX
GN 8350 Wing Screws (Stainless Steel)	QVX
GN 5064 T-Handles (Stainless Steel, Hygienic Design)	QVX

Technical Information

ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order

GN 5063-80-M10-MT

- | | |
|--------------|--|
| ¹ | Handle diameter d ₁ |
| ² | Thread d ₂ (Bore d ₃) |
| ³ | Finish |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

