



3 Type
D With revolving handle

Universal table

Dimensions in: millimeters - inches

| 1 d ₁ | 2 d ₂ Pilot hole | d ₄ | d ₅ | t | b | l ₁ -0.5 | l ₂ | l ₃ | l ₄ | d ₃ |
|-------------------------|---------------------------------------|----------------|----------------|------------|------------|---------------------|----------------|----------------|----------------|----------------|
| 80 3.15 | P 6 | 24 0.94 | 20 0.79 | 15 0.59 | 19 0.75 | 23 0.91 | 40 1.57 | 12 0.47 | 40 1.57 | M 6 |
| 100 3.94 | P 8 | 36 1.42 | 30 1.18 | 22 0.87 | 20 0.79 | 31 1.22 | 44 1.73 | 14 0.55 | 50 1.97 | M 8 |
| 130 5.12 | P 8 | 40 1.57 | 40 1.57 | 20 0.79 | 22 0.87 | 30 1.18 | 47 1.85 | 13 0.51 | 60 2.36 | M 8 |

Specification

- Plastic
Duroplast (Phenolic PF)
- High strength reinforced
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Hub bushing
Steel, blackened finish, molded-in
- Revolving handles
- Plastic, Duroplast
Black, shiny finish
- Hex socket head threaded spindle
Steel matte finish, chrome plated
- *Plastic Characteristics* → page QVX
- *ISO Fundamental Tolerances* → page QVX
- RoHS compliant

On request

- Other modifications such as inch and metric blind bores, threads, etc.

Information

EN 527.2 control knobs with a multi-lobed rim and revolving handle are very sturdy control knobs which, can be used either as control knobs or for clamping purposes.

Worth mentioning is the deliberately large hub. They also lend themselves to applications where a large contact face or a large bore is required.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Countersunk Washers GN 184 (for Axial Mounting)* → page QVX

| | |
|--|---------------------------------------|
| How to order EN 527.2-100-P8-D | 1 Knob diameter d ₁ |
| | 2 Pilot hole d ₂ |
| | 3 Type |