

SS Stainless Steel

4 Type (Base)

- D0 Without rubber pad / cap
- B0 Without rubber pad / cap, with 2 mounting holes
- D1 With rubber cap, clipped on, black
- D3 With rubber pad, vulcanized, black







Inch table

Dimensions in: inches - millimeters

d ₁	d ₂	l ₁								l ₇	d ₃	m	h ₁	h ₆	s
		Version S / SK				Version U / UK									
1.57 40	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.21 5.4	1.18 30	0.08 2	0.14 3.5	0.06 1.5
1.57 40	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.21 5.4	1.18 30	0.08 2	0.14 3.5	0.06 1.5
1.57 40	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.22 31	0.21 5.4	1.18 30	0.08 2	0.14 3.5	0.06 1.5
1.57* 40	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.21 5.4	1.18 30	0.08 2	0.14 3.5	0.06 1.5
1.97 50	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.26 6.6	1.50 38	0.10 2.5	0.16 4	0.08 2
1.97 50	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.26 6.6	1.50 38	0.10 2.5	0.16 4	0.08 2
1.97 50	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.26 6.6	1.50 38	0.10 2.5	0.16 4	0.08 2
1.97 50	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.26 6.6	1.50 38	0.10 2.5	0.16 4	0.08 2
2.36 60	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.26 6.6	1.89 48	0.10 2.5	0.18 4.5	0.08 2
2.36 60	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.26 6.6	1.89 48	0.10 2.5	0.18 4.5	0.08 2
2.36 60	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.26 6.6	1.89 48	0.10 2.5	0.18 4.5	0.08 2
2.36 60	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.26 6.6	1.89 48	0.10 2.5	0.18 4.5	0.08 2
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	1.02 26	0.33 8.5	2.52 64	0.12 3	0.20 5	0.08 2
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.14 29	0.33 8.5	2.52 64	0.12 3	0.20 5	0.08 2
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.33 8.5	2.52 64	0.12 3	0.20 5	0.08 2
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.50 38	0.33 8.5	2.52 64	0.12 3	0.20 5	0.08 2
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	1.77 45	0.33 8.5	2.52 64	0.12 3	0.20 5	0.08 2

* Not available in type B0

d ₁	d ₂	h ₃	h ₄	h ₅	A/F ₁	A/F ₂	A/F ₃	A/F ₇	t
1.57 40	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
1.57 40	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
1.57 40	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
1.57 40	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
1.97 50	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
1.97 50	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
1.97 50	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
1.97 50	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
2.36 60	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
2.36 60	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
2.36 60	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
2.36 60	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
3.15 80	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
3.15 80	3/8 x 16	0.47 12	-	-	11/16	-	-	1/2	0.39 10
3.15 80	1/2 x 13	0.47 12	-	-	11/16	-	-	5/8	0.47 12
3.15 80	5/8 x 11	-	0.71 18	0.59 15	-	1/2	5/16	7/8	0.63 16
3.15 80	3/4 x 10	-	0.75 19	0.59 15	-	9/16	7/16	1	0.79 20

Stud / socket versions		
 <p>5 S Without nut SK With nut</p>	 <p>5 T** Without nut TK** With nut</p>	 <p>5 U Without nut UK With nut</p>
External hex at the bottom at d ₂ 3/8 x 16, 1/2 x 13 M 8, M 10, M 12	Wrench flat at the bottom at d ₂ - M 16, M 20, M 24	Internal hex at the top, wrench flat at the bottom at d ₂ 5/8 x 11, 3/4 x 10 M 16, M 20, M 24
 <p>5 V** Without nut VK** With nut</p>	 <p>5 W** With adjustable sleeve</p>	 <p>5 X Tapped socket type</p>
External hex at the top, wrench flat at the bottom at d ₂ - M 16, M 20, M 24	Covered thread, wrench flat at the bottom at d ₂ - M 16, M 20, M 24	External hex with tapped socket at d ₂ 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20

** Only available with Metric thread

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10



Metric table

Dimensions in: millimeters - *inches*

d ₁	d ₂	l ₁	Version S / SK				Version T / TK and U / UK						Version V / VK				Version W				l ₇ Version X
			40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
40 1.57	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98	
40 1.57	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10	
40 1.57	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	31 1.22	
40* 1.57	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-	-	-	-	-	-	-	-	37 1.46	
50 1.97	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98	
50 1.97	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10	
50 1.97	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
50 1.97	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-	-	-	-	-	-	-	-	37 1.46	
60 2.36	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98	
60 2.36	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10	
60 2.36	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
60 2.36	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	37 1.46	
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	26 1.02	
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	29 1.14	
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	38 1.50	
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	100 3.94	125 4.92	150 5.91	200 7.87	134 5.28	159 6.26	184 7.24	234 9.21	45 1.77	
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	100 3.94	150 5.91	200 7.87	-	159 6.26	209 8.23	259 10.20	-	-	

* Not available in type B0

d ₁	d ₂	d ₃	d ₅	h ₁	h ₃	h ₄	h ₅	h ₆	l ₄	l ₅	l ₆	A/F ₁	A/F ₂	A/F ₃	A/F ₄	A/F ₅	A/F ₆	A/F ₇	m	s	t
40 1.57	M 8	5.4 0.21	-	2 0.08	11 0.43	-	-	3.5 0.14	-	-	-	17 0.67	-	-	-	-	-	14 0.55	30 1.18	1.5 0.06	8 0.31
40 1.57	M 10	5.4 0.21	-	2 0.08	11 0.43	-	-	3.5 0.14	-	-	-	17 0.67	-	-	-	-	-	14 0.55	30 1.18	1.5 0.06	10 0.39
40 1.57	M 12	5.4 0.21	-	2 0.08	11 0.43	-	-	3.5 0.14	-	-	-	17 0.67	-	-	-	-	-	17 0.67	30 1.18	1.5 0.06	12 0.47
40 1.57	M 16	5.4 0.21	-	2 0.08	-	17 0.67	14 0.55	3.5 0.14	-	-	-	-	12 0.47	8 0.31	-	-	-	22 0.87	30 1.18	1.5 0.06	16 0.63
50 1.97	M 8	6.6 0.26	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	17 0.67	-	-	-	-	-	14 0.55	38 1.50	2 0.08	8 0.31
50 1.97	M 10	6.6 0.26	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	17 0.67	-	-	-	-	-	14 0.55	38 1.50	2 0.08	10 0.39
50 1.97	M 12	6.6 0.26	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	17 0.67	-	-	-	-	-	17 0.67	38 1.50	2 0.08	12 0.47
50 1.97	M 16	6.6 0.26	-	2.5 0.10	-	17 0.67	14 0.55	4 0.16	-	-	-	-	12 0.47	8 0.31	-	-	-	22 0.87	38 1.50	2 0.08	16 0.63
60 2.36	M 8	6.6 0.26	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	17 0.67	-	-	-	-	-	14 0.55	48 1.89	2 0.08	8 0.31
60 2.36	M 10	6.6 0.26	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	17 0.67	-	-	-	-	-	14 0.55	48 1.89	2 0.08	10 0.39
60 2.36	M 12	6.6 0.26	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	17 0.67	-	-	-	-	-	17 0.67	48 1.89	2 0.08	12 0.47
60 2.36	M 16	6.6 0.26	24 0.94	2.5 0.10	-	17 0.67	14 0.55	4.5 0.18	45 1.77	45 1.77	29 1.14	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	48 1.89	2 0.08	16 0.63
80 3.15	M 8	8.5 0.33	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	17 0.67	-	-	-	-	-	14 0.55	64 2.52	2 0.08	8 0.31
80 3.15	M 10	8.5 0.33	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	17 0.67	-	-	-	-	-	14 0.55	64 2.52	2 0.08	10 0.39
80 3.15	M 12	8.5 0.33	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	17 0.67	-	-	-	-	-	17 0.67	64 2.52	2 0.08	12 0.47
80 3.15	M 16	8.5 0.33	24 0.94	3 0.12	-	18 0.71	15 0.59	5 0.20	45 1.77	45 1.77	29 1.14	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	64 2.52	2 0.08	16 0.63
80 3.15	M 20	8.5 0.33	30 1.18	3 0.12	-	19 0.75	15 0.59	5 0.20	56 2.20	56 2.20	37 1.46	-	15 0.59	10 0.39	13 0.51	16 0.63	24 0.94	27 1.06	64 2.52	2 0.08	20 0.79
80 3.15	M 24	8.5 0.33	35 1.38	3 0.12	-	22 0.87	18 0.71	5 0.20	67 2.64	67 2.64	42 1.65	-	19 0.75	12 0.47	17 0.67	20 0.79	30 1.18	-	64 2.52	2 0.08	-

Specification

- Base
Stainless steel AISI 304
Plain, tumbled finish
- Threaded stud / tapped socket
Stainless steel AISI 303
- Inch size hex nut ANSI / ASME B18.2.2
Stainless steel AISI 304
- Metric size hex nut ISO 4032
Stainless steel AISI 304
- Rubber cap
TPE (Santoprene®) ≈ 80 shore A
- Clipped on
- Black
- Rubber pad
NBR (Perbunan®) 70 ±5 shore A
- Vulcanized, non-skid
- Black
- Load Rating Information → page 2121
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Stud versions T / TK, V / VK and W with Inch thread with certain minimum quantities

Information


GN 41 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the stud / socket versions make these leveling feet universally applicable. The base with the rubber pad / cap protects sensitive surfaces and reduces lateral slippage. The type B0 can also be fastened to the mounting surface via the two mounting holes provided.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...


- Leveling Feet GN 40 (Steel, without Mounting Hole) → page 1516
- Leveling Feet GN 42 (Steel, with Mounting Hole) → page 1526
- Leveling Feet GN 42 (Steel, with Slotted Mounting Hole, Rectangular Shape) → page 1530
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Mounting Hole) → page 1532 / 1532
- Leveling Feet GN 44 / GN 45 (Stainless Steel AISI 316, with / without Mounting Hole) → page 1524 / 1540
- Threaded Tube Ends EN 448 (Plastic) → page 1576 / 1578
- Threaded Tube Inserts GN 992 / GN 992.5 (Aluminum / Stainless Steel) → page 1581

How to order (Inch)	
1	Base diameter d ₁
2	Thread d ₂
3	Length l ₇ (Length l ₁)
4	Type (Base)
5	Stud / socket version



GN 41-40-5/16X18-25-B0-X

How to order (Metric)	
1	Base diameter d ₁
2	Thread d ₂
3	Length l ₁ (Length l ₂ , l ₃ , l ₇)
4	Type (Base)
5	Stud / socket version



GN 41-80-M16-75-D0-TK

 3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10
