



**3 Type**

- E With tapped blind bore
- D With tapped through bore

**Inch table**

Dimensions in: inches - millimeters

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type E	b	h	t <sub>1</sub> min.
1.02 25.9	10 x 32	0.43 10.9	0.51 13.0	0.24 6.1
1.26 32.0	1/4 x 20	0.51 13.0	0.59 15.0	0.31 7.9
1.57 39.9	5/16 x 18	0.61 15.5	0.67 17.0	0.31 7.9

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Type E			<b>2</b> d <sub>3</sub> Type D			d <sub>4</sub>	b	h	t <sub>1</sub> min.	t <sub>2</sub>
20 0.79	M 4	-	-	-	-	-	-	9.5 0.37	11 0.43	6 0.24	-
26 1.02	M 5	M 6	-	-	-	-	-	11 0.43	13 0.51	6 0.24	-
32 1.26	M 5	M 6	M 8	M 5	M 6	-	6.5 0.26	13 0.51	15 0.59	6 0.24	12 0.47
40 1.57	M 5	M 6	M 8	M 5	M 6	M 8	9 0.35	15.5 0.61	17 0.67	6 0.24	12 0.47
48 1.89	M 8	-	-	M 8	-	-	9 0.35	19 0.75	19 0.75	10 0.39	16 0.63
56 2.20	M 10	-	-	M 10	-	-	11 0.43	21 0.83	23 0.91	13 0.51	20 0.79

**Specification**

- Wing body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, matte finish
- Tapped insert  
Brass
- Plastic Characteristics → page 2135
- RoHS compliant

**Information**

Due to their low height EN 532 wing nuts offer a comfortable grip for quick two finger clamping applications.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Wing nuts EN 532.1 (with Protruding Hub) → page 668
- Wing Nuts EN 634 → page 660
- Small Wing Nuts EN 640 → www.jwwinco.com

How to order <b>EN 532-1.02-10X32-E</b>	<b>1</b> Handle diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub>
	<b>3</b> Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4