




Metric table

Dimensions in: millimeters / inches				
Length l	h ₁	h ₂	h ₃	F ₁ Static load Folded out
100 3.94	34 1.34	44.5 1.75	55 2.17	500 N 112 lbf
120 4.72	34 1.34	44.5 1.75	55 2.17	500 N 112 lbf
180 7.09	34 1.34	44.5 1.75	55 2.17	500 N 112 lbf

Specification

Handle

- Steel
- Chrome plated
- Stainless steel AISI 303
- Matte shot-blasted finish

CR
NI

Location flange

- Plastic, Polyamide (PA)
- Operating temperature up to 212 °F (100 °C)
- Black, matte finish

Covers

- Plastic, Polyamide (PA)
- Operating temperature up to 212 °F (100 °C)
- Black-gray, matte finish

RoHS

Folding handles GN 425.5 are used in applications where the handle must not protrude or protrude only slightly. The handle is held in both end positions by means of a spring-loaded (spring disks) thrust bolt. The static load capacity value given in the table is an approximate value which, if exceeded, may result in permanent deformation or fracture of the plastic attachment part. Folding handles GN 425.2 may be used as an alternative.

see also...	Page
GN 425.8 Folding Handles with Recessed Tray (Steel / Stainless Steel, with Recessed Tray)	QVX
GN 425.2 Folding Handles	QVX
EN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Load Capacity Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1 Length l
	2 Finish (Material)

GN 425.5-100-CR