



SS Stainless Steel

Inch table

Dimensions in: inches - millimeters

d ₁	d ₂	Length l				b	d ₃	h ₁	h ₂	t min.
1.02 26	10 x 32	0.39 10	0.63 16	-	-	0.43 11	0.39 10	0.39 10	0.18 4.5	0.31 8
1.02 26	1/4 x 20	0.63 16	0.79 20	0.98 25	-	0.43 11	0.39 10	0.39 10	0.18 4.5	0.31 8
1.34 34	1/4 x 20	0.79 20	0.98 25	1.18 30	-	0.51 13	0.47 12	0.47 12	0.20 5	0.39 10
1.34 34	5/16 x 18	0.63 16	0.79 20	1.18 30	-	0.51 13	0.47 12	0.47 12	0.20 5	0.39 10

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂	Length l				b	d ₃	h ₁	h ₂	t min.
20 0.79	M 4	6 0.24	10 0.39	-	-	9 0.35	8 0.31	8 0.31	3.5 0.14	7 0.28
26 1.02	M 4	12 0.47	16 0.63	-	-	11 0.43	10 0.39	10 0.39	4.5 0.18	7 0.28
26 1.02	M 5	10 0.39	12 0.47	16 0.63	-	11 0.43	10 0.39	10 0.39	4.5 0.18	8 0.31
26 1.02	M 6	12 0.47	16 0.63	20 0.79	25 0.98	11 0.43	10 0.39	10 0.39	4.5 0.18	8 0.31
34 1.34	M 6	16 0.63	20 0.79	25 0.98	30 1.18	13 0.51	12 0.47	12 0.47	5 0.20	10 0.39
34 1.34	M 8	16 0.63	20 0.79	25 0.98	30 1.18	13 0.51	12 0.47	12 0.47	5 0.20	9 0.35

Specification

- Stainless steel precision casting
 - AISI CF-8 **NI**
 - AISI 316 **A4**
 - Matte shot-blasted finish **MT**
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

Wing screws GN 433 and wing nuts GN 434 clamp and fasten parts easily without tools. The ergonomic shape and the projecting collar make operation easier.

The version in stainless steel A4 can be used in especially aggressive environments.

see also...

- Wing Nuts GN 834 (Stainless Steel) → page 676
- Wing Screws GN 835 (Stainless Steel) → page 677

How to order (Inch wing nut)	1 Material
GN 434-NI-34-1/4X20-MT	2 Handle diameter d ₁
	3 Thread d ₂
	5 Finish

How to order (Metric wing screw)	1 Material
GN 433-NI-26-M6-16-MT	2 Handle diameter d ₁
	3 Thread d ₂
	4 Length l
	5 Finish