



SS Stainless Steel

3 Type
E With tapped blind bore

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	d ₄	h ₁	h ₂	t min.
45 1.77	M 6	19 0.75	25 0.98	22.5 0.89	12 0.47
63 2.48	M 8	26 1.02	28 1.10	25 0.98	15 0.59
80 3.15	M 10	32 1.26	35 1.38	30 1.18	17 0.67
100 3.94	M 12	36 1.42	42 1.65	36 1.42	20 0.79
130 5.12	M 16	43 1.69	47 1.85	40 1.57	22 0.87

Specification

- Three-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Tapped insert
Stainless steel AISI 303
- *Stainless Steel Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

On request

- Special inch or metric size tapped blind or tapped through bores larger than listed, threaded studs, cross holes, and set screw holes

Information

Due to the shape of EN 5330.5 three-lobed knobs, higher torque can be achieved. The material is able to withstand relatively high impact.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Three-Lobed Knobs GN 5345 (Stainless Steel)* → page QVX

<p>How to order</p> <p>EN 5330.5-63-M8-E</p>	1	Handle diameter d ₁
	2	Thread d ₂
	3	Type