



SS Stainless Steel

4 Type

- A** With lanyard ring only
- H** With retaining cable
- K** With ball chain

Metric table

Dimensions in: millimeters - inches

d₁	d₂	Length l					d₃	h₁	h₂	h₃	r ≈	s
40 1.57	M 8	20 0.79	30 1.18	40 1.57	-	14 0.55	24 0.94	12 0.47	3.2 0.13	22.3 0.88	2.8 0.11	
50 1.97	M 10	20 0.79	30 1.18	40 1.57	-	18 0.71	30 1.18	17 0.67	3.9 0.15	29.6 1.17	3.2 0.13	
60 2.36	M 12	20 0.79	30 1.18	40 1.57	50 1.97	20 0.79	38 1.50	20 0.79	3.9 0.15	30.7 1.21	3.2 0.13	

Specification

- Star knob
Stainless steel AISI 316L
- Hub welded
- Matte shot-blasted finish
- Threaded stud
Stainless steel AISI 304
- Lanyard ring GN 111.6
Stainless steel AISI 301
- Ball chain GN 111.5 (Type K)
Stainless steel AISI 301
- Retaining cable GN 111.2 (Type H)
Stainless steel
Coated with clear plastic
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

Information

GN 5334.13 star knobs with loss protection can be attached to a base element with the help of a ball chain or a retaining cable.
The star knobs are supplied ready assembled (with lanyard ring, with lanyard ring and retaining cable, or with lanyard ring and ball chain).

see also...

- [Ball Chains GN 111.5 \(Stainless Steel\)](#) → page 1236
- [Retaining Cables GN 111.2 \(Stainless Steel\)](#) → page 1238
- [Spiral Retaining Cables GN 111.4](#) → page 1237
- [Lanyard Rings GN 111.6 \(Stainless Steel\)](#) → page 1241
- [More Star Knobs with Loss Protections GN 111.7](#) → page 2046

On request

- Ball chains / retaining cables with other lengths
- With spiral retaining cable GN 111.4
- Other GN / DIN series with loss protection

<p>How to order (Threaded stud)</p> <p>GN 5334.13-60-M12-40-A</p>	1 Handle diameter d ₁
	2 Thread d ₂
	3 Length l
	4 Type