



Inch | Metric



3 Type

- A** Blank type
- C** With plain blind bore, tol. H7
- D** With tapped through bore
- E** With tapped blind bore

Inch table

1		2		Dimensions in: inches / millimeters						
d ₁	d ₂ Thread Type E	d ₄ +0.02	h ₁ -0.04	h ₂ ≈	t ₁ min.	t ₂				
1.57 40	1/4 x 20	5/16 x 18	0.55 14	0.98 25	0.49 12.5	0.59 15	0.51 13			
1.97 50	5/16 x 18	3/8 x 16	0.71 18	1.26 32	0.63 16	0.71 18	0.63 16			
2.36 60	3/8 x 16	1/2 x 13	0.79 20	1.57 40	0.79 20	0.87 22	0.79 20			
2.76 70	1/2 x 13	5/8 x 11	0.98 25	1.81 46	0.91 23	1.10 28	0.79 20			

Metric table

1		2		Dimensions in: millimeters / inches						
d ₁	d ₂ Thread Type E	Type D	d ₃ H7 Bore Type C	d ₄ +0.5	h ₁ -1	Type A	Type C Type D Type E	h ₂ ≈	t ₁ min.	t ₂
40 1.57	M 6	M 8	M 8	B 8	14 0.55	26 1.02	25 0.98	12.5 0.49	15 0.59	13 0.51
50 1.97	M 8	M 10	M 10	B 10	18 0.71	33 1.30	32 1.26	16 0.63	18 0.71	16 0.63
60 2.36	M 10	M 12	M 12	B 12	20 0.79	41 1.61	40 1.57	20 0.79	22 0.87	20 0.79
70 2.76	M 12	M 16	M 16	B 16	25 0.98	47 1.85	46 1.81	23 0.91	28 1.10	20 0.79

Specification

Aluminum

- Matte, tumbled finish **MT**
 - Flash mark not visible
 - Polished finish **PL**
- (only available in Type C, D, E in metric sizes)

RoHS

On request

- Special threads, bores, or threaded studs in matte finish only
- Other modifications such as cross holes and set screw holes

Technical Information

Cross Holes GN 110 QVX
ISO Fundamental Tolerances QVX

Star knobs GN 5336 are forged; therefore, a close grain structure is maintained providing a high tensile strength and a smooth surface. Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

	Page
DIN 6336 Star Knobs (Aluminum)	QVX
GN 5334 Star Knobs (Stainless Steel)	QVX

How to order (Blank type)

GN 5336-60-A-MT

1	Handle diameter d ₁
2	Type
3	Finish

How to order (Inch)

GN 5336-40-1/4X20-E-MT

1	Handle diameter d ₁
2	Thread d ₂
3	Type
4	Finish

How to order (Metric)

GN 5336-60-B12-C-PL

1	Handle diameter d ₁
2	Bore d ₃ (Thread d ₂)
3	Type
4	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

