



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	h	k
M 3	12 0.47	6 0.24	3 0.12	2.5 0.10
M 4	16 0.63	8 0.31	4 0.16	3.5 0.14
M 5	20 0.79	10 0.39	5 0.20	4 0.16
M 6	24 0.94	12 0.47	6 0.24	5 0.20
M 8	30 1.18	16 0.63	8 0.31	6 0.24
M 10	36 1.42	20 0.79	10 0.39	8 0.31
M 12	40 1.57	22 0.87	12 0.47	10 0.39

Specification

- Steel
  - Property class 5
  - Visible face fine turned
  - Blackened finish **—**
  - Zinc plated, blue passivated finish **ZB**
- Stainless steel AISI 303 **NI**  
Matte shot-blasted finish
- Strength Values of Nuts → page 2127
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

DIN 467 knurled nuts can be tightened and loosened easily without tools.  
 see also...  
 • Knurled Nuts GN 536 (Stainless Steel) → page 702  
 • Knurled Nuts DIN 6303 (Stainless Steel) → page 699  
 • Knurled Nuts DIN 466 (High Type) → page 704  
 • Knurled Nuts DIN 466 (High Type, with Loss Protection GN 111.7) → page 2046

On request

- Version in stainless steel (A4 quality)

How to order (Steel, blackened finish)	1 Thread d <sub>1</sub>
<b>DIN 467-M3</b>	
How to order (Steel, zinc plated)	1 Thread d <sub>1</sub>
<b>DIN 467-M12-ZB</b>	2 Finish
How to order (Stainless steel)	1 Thread d <sub>1</sub>
<b>DIN 467-M8-NI</b>	2 Material

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4