



Metric



elesa
Original design VCHT.

3 Type

- E** With cover cap (tapped blind bore)
- D** Without cover cap (tapped through bore)

Metric table

1 d ₁	2 d ₂ Type E		2 d ₃ Type D		d ₄	d ₅	h ₁	h ₂	t
32 1.26	M 5	M 6	M 5	M 6	12 0.47	10 0.39	22.5 0.89	8.5 0.33	16.5 0.65
40 1.57	M 6	M 8	M 6	M 8	14 0.55	12 0.47	27 1.06	10 0.39	20 0.79
50 1.97	M 8	M 10	M 8	M 10	18 0.71	15 0.59	30 1.18	10 0.39	20 0.79
63 2.48	M 10	M 12	M 10	M 12	20 0.79	19 0.75	35.5 1.40	14 0.55	29 1.14
74 2.91	M 12	M 16	M 12	M 16	25 0.98	17 0.67	39.5 1.56	15 0.59	29 1.14

Dimensions in: millimeters / inches

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -22 °F to +266 °F (-30 °C to +130 °C)
- Black, matte finish

Hub insert

Steel, zinc plated

Cover cap for type E

- Plastic, Polypropylen (PP)
- Black, RAL 9005, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Yellow, RAL 1021, matte finish
- Blue, RAL 5024, matte finish
- Red, RAL 3000, matte finish
- Green, RAL 6017, matte finish

- **DSW**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

Five-lobed knobs EN 5337.1 with protruding hub have important advantages:

The contact surface of the hub is exactly perpendicular to the bore and the entire diameter is made of steel. The protruding steel hub allows a perfect cross-pin connection.

see also...

	Page
EN 5337.2 Five-Lobed Knobs (Brass / Steel Insert)	QVX
EN 5337.6 Five-Lobed Knobs (Softline)	QVX
EN 5337.7 Five-Lobed Knobs (Stainless Steel Insert)	QVX

Technical Information

Plastic Characteristics

Page

QVX

How to order (Without cover cap)

EN 5337.1-40-M8-D

- 1** Handle diameter d₁
- 2** Thread d₃
- 3** Type

How to order (With cover cap)

EN 5337.1-32-M5-E-DSW

- 1** Handle diameter d₁
- 2** Thread d₂
- 3** Type
- 4** Color of the cover cap

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

