


**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub> Bore for shaft tolerance h11	<sup>2</sup> d <sub>2</sub> Bore for shaft tolerance h11	d <sub>3</sub> Clamping thread	k	l <sub>1</sub>	l <sub>2</sub>	m	s <sub>1</sub> Square	s <sub>2</sub> Square	Adjustable lever kit for d <sub>3</sub> 
B 8	B 8	M 4	14 0.55	37 1.46	13.5 0.53	10 0.39	-	-	GN 511-M4-14
B 10	B 8	M 5	16 0.63	46 1.81	17 0.67	12 0.47	8 0.31	-	GN 511-M5-16
B 10	B 10	M 5	16 0.63	46 1.81	17 0.67	12 0.47	8 0.31	8 0.31	GN 511-M5-16
B 12	B 8	M 5	16 0.63	48 1.89	17 0.67	14 0.55	10 0.39	-	GN 511-M5-16
B 12	B 12	M 5	16 0.63	48 1.89	17 0.67	14 0.55	10 0.39	10 0.39	GN 511-M5-16
B 15	B 10	M 6	20 0.79	58 2.28	20.5 0.81	17 0.67	12 0.47	8 0.31	GN 511-M6-20
B 15	B 12	M 6	20 0.79	58 2.28	20.5 0.81	17 0.67	12 0.47	10 0.39	GN 511-M6-20
B 15	B 15	M 6	20 0.79	58 2.28	20.5 0.81	17 0.67	12 0.47	12 0.47	GN 511-M6-20
B 16	B 12	M 6	20 0.79	59 2.32	20.5 0.81	18 0.71	-	10 0.39	GN 511-M6-20
B 16	B 16	M 6	20 0.79	59 2.32	20.5 0.81	18 0.71	-	-	GN 511-M6-20
B 20	B 15	M 6	25 0.98	65 2.56	21.5 0.85	22 0.87	16 0.63	12 0.47	GN 511-M6-25
B 20	B 16	M 6	25 0.98	65 2.56	21.5 0.85	22 0.87	16 0.63	-	GN 511-M6-25
B 20	B 20	M 6	25 0.98	65 2.56	21.5 0.85	22 0.87	16 0.63	16 0.63	GN 511-M6-25

**Specification**

- Body  
Aluminum  
- Matte, tumbled finish  
- Black anodized finish
- Socket cap screws DIN 912  
Stainless steel AISI 304
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**MT  
ELS**

**Accessory**

- Adjustable lever kits GN 511 → page 1829

**Information**

In the standard version, the clamping screws are DIN 912 socket cap screws with hexagonal socket. They can be replaced by GN 511 adjustable lever kits (part number, see dimensional table).

see also...

- Rods / Tubes GN 480.1 → page 1838
- Swivel Clamp Connector Joints GN 490 → page 1814
- Two-Way Connector Clamps GN 131 → page 1770

How to order	
<sup>1</sup>	Bore d <sub>1</sub>
<sup>2</sup>	Bore d <sub>2</sub>
<sup>3</sup>	Finish

**GN 474-B12-B12-ELS**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

