



**Specification**



- Five-lobed knob  
Plastic  
Technopolymer (Polypropylene PP)
  - Reinforced, shock-resistant
  - Temperature resistant up to 194 °F (90 °C)
  - Black, matte finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- Color of the cover cap (matte finish)
 

Black, RAL 9005	● DSW
Orange, RAL 2004	● DOR
Gray, RAL 7035	● DGR
Yellow, RAL 1021	● DGB
Blue, RAL 5024	● DBL
Red, RAL 3000	● DRT
Green, RAL 6017	● DGN
- *Plastic Characteristics* → page 2135
- RoHS compliant

**Information**

The special type of technopolymer used and the matte finish make these EN 5337.2 five-lobed knobs elegant and “soft” to touch. The operator obtains a strong clamping action without any discomfort due to its ergonomic design: five lobes, blended radius and well proportioned rim height assure a natural, safe and comfortable grip.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Five-Lobed Knobs EN 5337.7 (Stainless Steel Threaded Stud)* → page 605
- *Solid Five-Lobed Knobs EN 5337.4 (Stainless Steel Threaded Stud)* → page 608
- *Softline Five-Lobed Knobs EN 5337.6* → page 611
- *Five-Lobed Knobs EN 5337.2 with Loss Protection GN 111.7* → page 2046

How to order	
1	Handle diameter $d_1$
2	Thread $d_2$
3	Length $l$
4	Color of the cover cap

1 2 3 4  
**EN 5337.2-1.57-5/16X18-1.00-DSW**

**Inch table**

Dimensions in: inches - millimeters

<b>1</b>	<b>2</b>		<b>3</b>				<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub> ≈</b>
<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>		<b>Length l</b>							
0.98* 24.9	10 x 32		-	0.50 12.7	0.75 19.1	-	0.51 13.0	0.31 7.9	0.75 19.1	0.31 7.9
1.26 32.0	1/4 x 20		-	0.50 12.7	0.75 19.1	1.00 25.4	0.59 15.0	0.39 9.9	0.91 23.1	0.39 9.9
1.57 39.9	1/4 x 20		-	0.50 12.7	1.00 25.4	-	0.67 17.0	0.51 13.0	1.06 26.9	0.47 11.9
1.57 39.9	5/16 x 18		-	0.75 19.1	1.00 25.4	-	0.67 17.0	0.51 13.0	1.06 26.9	0.47 11.9
1.97 50.0	5/16 x 18		3/8 x 16	1.00 25.4	1.50 38.1	-	0.75 19.1	0.59 15.0	1.26 32.0	0.55 14.0
2.48 63.0	3/8 x 16		-	1.25 31.8	2.00 50.8	-	0.87 22.1	0.75 19.1	1.46 37.1	0.63 16.0
2.48 63.0	1/2 x 13		-	1.50 38.1	-	-	0.87 22.1	0.75 19.1	1.46 37.1	0.63 16.0
2.91 73.9	1/2 x 13		-	1.25 31.8	2.00 50.8	-	1.02 25.9	0.67 17.0	1.71 43.4	0.87 22.1

**Metric table**

Dimensions in: millimeters - inches

<b>1</b>	<b>2</b>		<b>3</b>				<b>d<sub>3</sub></b>	<b>d<sub>4</sub></b>	<b>h<sub>1</sub></b>	<b>h<sub>2</sub> ≈</b>						
<b>d<sub>1</sub></b>	<b>d<sub>2</sub></b>		<b>Length l</b>													
25 0.98	M 4	-	6 0.24	10 0.39	-	-	-	-	13 0.51	8 0.31	19 0.75	8 0.31				
25 0.98	M 5	M 6	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	-	-	13 0.51	8 0.31	19 0.75	8 0.31		
32 1.26	M 6	-	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	-	-	-	15 0.59	10 0.39	23 0.91	10 0.39		
32 1.26	M 8	-	16 0.63	20 0.79	30 1.18	40 1.57	50 1.97	-	-	-	15 0.59	10 0.39	23 0.91	10 0.39		
40 1.57	M 6	-	20 0.79	25 0.98	30 1.18	-	-	-	-	-	17 0.67	13 0.51	27 1.06	12 0.47		
40 1.57	M 8	-	16 0.63	20 0.79	25 0.98	30 1.18	35 1.38	40 1.57	45 1.77	50 1.97	55 2.17	70 2.76	17 0.67	13 0.51	27 1.06	12 0.47
40 1.57	M 10	-	20 0.79	25 0.98	30 1.18	40 1.57	50 1.97	-	-	-	-	-	17 0.67	13 0.51	27 1.06	12 0.47
50 1.97	M 8	-	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	50 1.97	-	-	-	-	19 0.75	15 0.59	32 1.26	14 0.55
50 1.97	M 10	M 12	20 0.79	30 1.18	40 1.57	50 1.97	60 2.36	-	-	-	-	-	19 0.75	15 0.59	32 1.26	14 0.55
63 2.48	M 10	M 12	20 0.79	30 1.18	40 1.57	50 1.97	60 2.36	-	-	-	-	-	22 0.87	19 0.75	37 1.46	16 0.63
74 2.91	M 12	-	30 1.18	50 1.97	70 2.76	-	-	-	-	-	-	-	26 1.02	17 0.67	43.5 1.71	22 0.87
74 2.91	M 14	-	50 1.97	-	-	-	-	-	-	-	-	-	26 1.02	17 0.67	43.5 1.71	22 0.87
74 2.91	M 16	-	30 1.18	40 1.57	50 1.97	60 2.36	70 2.76	-	-	-	-	-	26 1.02	17 0.67	43.5 1.71	22 0.87
84 3.31	M 12	M 16	30 1.18	50 1.97	70 2.76	-	-	-	-	-	-	-	28 1.10	22 0.87	44 1.73	21 0.83
95 3.74	M 16	-	50 1.97	-	-	-	-	-	-	-	-	-	32 1.26	19 0.75	46 1.81	21 0.83

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

