



3 Type

- S With skirt and pointer
- Z With pointer

Metric table

Dimensions in: millimeters - inches

1		2															
d ₁	Type S	Type Z	d ₂ H9 Bore	d ₃	d ₄	d ₅	d ₆	d ₇	e	h ₁	h ₂	h ₃	h ₄	h ₅	l ₁	l ₂	
32	1.26	-	B 6	14 0.55	19 0.75	-	M 4	36 1.42	6 0.24	27 1.06	-	3 0.12	-	19 0.75	19 0.75	-	
40	1.57	40 1.57	B 6	14 0.55	21 0.83	25 0.98	M 4	45 1.77	6 0.24	30 1.18	27 1.06	3 0.12	2 0.08	14 0.55	24 0.94	25 0.98	
50	1.97	50 1.97	B 8	15 0.59	25 0.98	30 1.18	M 5	56 2.20	7 0.28	36 1.42	33 1.30	3 0.12	2 0.08	20 0.79	30 1.18	31 1.22	
60	2.36	60 2.36	B 8	15 0.59	27 1.06	32 1.26	M 5	70 2.76	7 0.28	42 1.65	37 1.46	5 0.20	2 0.08	20 0.79	37 1.46	38 1.50	
70	2.76	70 2.76	B 10	18 0.71	30 1.18	35 1.38	M 6	80 3.15	10 0.39	48 1.89	44 1.73	5 0.20	2 0.08	25 0.98	42 1.65	45 1.77	

Specification

- Plastic
Knob body: Duroplast (PF)
Pointer: Technopolymer (Polyamide PA)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Insert
Brass: Size 32, 40 mm
Steel: Size 50, 60, 70 mm
- Arrow (Type S)
White
- Set screw DIN 916
Stainless steel
with internal hex and serrated point
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

On request

- Other modifications such as inch and metric blind bores, threads, etc.

Information

EN 5338 five-lobed control knobs are very appealing with a good gripping feel. The manufacturing technique has made it possible to produce them with no visible flash mark.

The pointer element is pressed into a groove on the hand knob hub which secures it from twisting.

Two socket set screws with serrated points ensure a secure attachment to the shaft.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Six-Lobed Skirted Control Knobs VBI (Phenolic Plastic) → page QVX

How to order	1	Outside diameter d ₁
	2	Bore d ₂
	3	Type

EN 5338-50-B8-S