



3 Type
A With bore
W With bolt

Metric table

1 d₁ Type A	1 d₂ Type W	2 k	d₃	d₄ Swivel bore	d₅ Thread	l₁	l₂	l₃	l₄	l₅	l₆	t	Clamping kit for d ₄ Type S	Clamping kit for d ₄ Type K
B 8	8 0.31	16 0.63	7 0.28	4.5 0.18	M 4	30 1.18	22 0.87	13 0.51	8 0.31	5.5 0.22	16 0.63	8 0.31	GN 511.1-M4-16-S	GN 511.1-M4-16-K
B 10	10 0.39	20 0.79	8.5 0.33	5.5 0.22	M 5	38 1.50	28 1.10	17 0.67	10 0.39	7 0.28	17 0.67	10 0.39	GN 511.1-M5-20-S	GN 511.1-M5-20-K
B 12	12 0.47	20 0.79	8.5 0.33	5.5 0.22	M 5	38 1.50	28 1.10	17 0.67	10 0.39	8 0.31	19 0.75	12 0.47	GN 511.1-M5-20-S	GN 511.1-M5-20-K
B 15	15 0.59	25 0.98	10 0.39	6.5 0.26	M 6	46 1.81	33.5 1.32	20 0.79	12.5 0.49	10 0.39	21 0.83	15 0.59	GN 511.1-M6-25-S	GN 511.1-M6-25-K
B 16	16 0.63	25 0.98	10 0.39	6.5 0.26	M 6	46 1.81	33.5 1.32	20 0.79	12.5 0.49	11 0.43	24 0.94	16 0.63	GN 511.1-M6-25-S	GN 511.1-M6-25-K
B 20	20 0.79	30 1.18	10 0.39	6.5 0.26	M 6	55 2.17	40 1.57	24 0.94	15 0.59	12 0.47	26 1.02	18 0.71	GN 511.1-M6-30-S	GN 511.1-M6-30-K

Dimensions in: millimeters - inches

Specification

- Body Aluminum
- Matte, tumbled finish **MT**
- Black anodized finish **ELS**
- Bolt (Type W)
Steel, zinc plated, blue chromated finish
- Set screw DIN 913 (Type A)
Stainless steel AISI 304
- Set screw DIN 915 (Type W)
Stainless steel AISI 304
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

Accessory

- Clamping kits GN 511.1 → page QVX

Information

GN 483 T-swivel mounting clamps can be combined with GN 482 swivel mounting clamps, GN 484 attachment swivel mounting clamps as well as GN 485 base plate swivel mounting clamps with the same k dimensions to mounting clamp joints. GN 511.1 clamping kits with screw (type S) and adjustable lever (type K) are available for this purpose (part number see dimensional table).

see also...

- *Rods / Tubes GN 480.1* → page QVX

How to order (With bore)

1 Bore d ₁
2 Width k
3 Type
4 Finish

GN 483-B12-20-A-MT

How to order (With bolt)

1 Diameter d ₂
2 Width k
3 Type
4 Finish

GN 483-20-30-W-ELS

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10