



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> a <sup>-0.3 -0.5</sup>	<sup>2</sup> d	e <sup>-0.5</sup>	h	k <sup>-0.5</sup>	For DIN 650 T-slots
8 0.31	M 6	13 0.51	10 0.39	6 0.24	8 0.31
10 0.39	M 8	15 0.59	12 0.47	6 0.24	10 0.39
12 0.47	M 10	18 0.71	14 0.55	7 0.28	12 0.47
14 0.55	M 12	22 0.87	16 0.63	8 0.31	14 0.55
16 0.63	M 14	25 0.98	18 0.71	9 0.35	16 0.63
18 0.71	M 16	28 1.10	20 0.79	10 0.39	18 0.71
22 0.87	M 20	35 1.38	28 1.10	14 0.55	22 0.87

**Specification**

- Heat-treated steel
  - Property class 10
  - Blackened finish
- *Strength Values of Nuts* → page 2127
- RoHS compliant

**Information**

GN 508.1 rhombus T-slot nuts can be inserted vertically into the T-slot.  
 see also...  
 • *T-Slot Nuts DIN 508* → page 1221

How to order <b>GN 508.1-14-M12</b>	<sup>1</sup> Nut width a
	<sup>2</sup> Thread d