



Metric



elesa
Original design IF / IFF

4 Type

- A With hand guard, one side
- B With hand guard, both sides

Metric table

1 d_1	2 d_2	3 l_2	d_3	d_4	l_1	l_3	l_4	t
30 1.18	M 8	20 0.79	64 2.52	46 1.81	112 4.41	4 0.16	4 0.16	20 0.79
30 1.18	M 10	20 0.79	64 2.52	46 1.81	112 4.41	4 0.16	4 0.16	18 0.71

Dimensions in: millimeters / inches

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature up to 266 °F (130 °C)
- Black, matte finish

Tapped insert

Brass

Threaded stud

Steel, zinc plated, blue passivated finish

RoHS

Cylindrical handles EN 539.2 are used as handles for electrical tools such as angle grinders, percussion drills etc. Their special feature is the hand guard on one or both sides.

see also...

	Page
EN 539 Fixed Cylindrical Handles	QVX
EN 519 Cylindrical Handles (with Molded-In Thread)	QVX

Technical Information

Plastic Characteristics	QVX
-------------------------	-----

How to order (Tapped type)

EN 539.2-30-M8-A

1	Handle diameter d_1
2	Thread d_2
4	Type

How to order (Threaded stud)

EN 539.2-30-M10-20-A

1	Handle diameter d_1
2	Thread d_2
3	Thread length l_2
4	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

