



Metric table

Dimensions in: millimeters - inches

¹ a ^{-0.3 -0.5}	² d Thread	e	h	k	s	For DIN 650 T-slots
10 0.39	M 8	15 0.59	12 0.47	6 0.24	0.65 0.03	10 0.39
12 0.47	M 10	18 0.71	14 0.55	7 0.28	0.65 0.03	12 0.47
14 0.55	M 12	22 0.87	16 0.63	8 0.31	1 0.04	14 0.55
18 0.71	M 16	28 1.10	20 0.79	10 0.39	1 0.04	18 0.71
22 0.87	M 20	35 1.38	28 1.10	14 0.55	1.6 0.06	22 0.87

Specification

- Heat-treated steel
- Property class **8**
Zinc plated, blue passivated finish
- Property class **10**
Blackened finish
- Strength Values of Nuts → page QVX
- RoHS compliant

Information

GN 508.2 T-slot nuts are dimensionally identical to DIN 508. However, they are fitted with a spring loaded ball on the side. This prevents unwanted movement of the nut, which is of great advantage especially when mounted vertically.

see also...

- T-Slot Nuts DIN 508 → page QVX

How to order GN 508.2-22-M20-10	¹ Nut width a
	² Thread d
	³ Property class

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10