



**SS** Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> <b>a</b> -0.3 -0.5	<sup>2</sup> <b>d</b>	<b>e</b> -0.5	<b>h</b>	<b>k</b> -0.5	For DIN 650 T-slots
8 0.31	M 6	13 0.51	10 0.39	6 0.24	8 0.31
10 0.39	M 8	15 0.59	12 0.47	6 0.24	10 0.39
12 0.47	M 10	18 0.71	14 0.55	7 0.28	12 0.47
14 0.55	M 12	22 0.87	16 0.63	8 0.31	14 0.55
16 0.63	M 14	25 0.98	18 0.71	9 0.35	16 0.63
18 0.71	M 16	28 1.10	20 0.79	10 0.39	18 0.71

**Specification**

- Stainless steel
  - AISI 316LHC (with thread)
  - AISI 304 (without thread)

• *Stainless Steel Characteristics* → page 2143

- RoHS compliant



**Information**

DIN 508 T-slot nuts are also available without thread. These can be adapted for special applications.

How to order (With thread) <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>DIN 508-14-M12-NI</b>	<b>1</b> Nut width a
	<b>2</b> Thread d
	<b>3</b> Material
How to order (Without thread) <sup>1</sup> <sup>3</sup> <b>DIN 508-18-NI</b>	<b>1</b> Nut width a
	<b>3</b> Material