



Metric



Metric table

b	Length l ±0.25	a	d₁	d₂	h	r	t min.
25 0.98	112 4.41	16 0.63	M 6	10 0.39	50 1.97	5 0.20	10 0.39
25 0.98	128 5.04	16 0.63	M 6	10 0.39	54 2.13	7 0.28	10 0.39
25 0.98	160 6.30	16 0.63	M 6	10 0.39	54 2.13	9 0.35	10 0.39
25 0.98	192 7.56	16 0.63	M 6	10 0.39	54 2.13	9 0.35	10 0.39
35 1.38	160 6.30	25 0.98	M 8	17 0.67	68 2.68	12.5 0.49	12 0.47
35 1.38	192 7.56	25 0.98	M 8	17 0.67	68 2.68	12.5 0.49	12 0.47
35 1.38	300 11.81	25 0.98	M 8	17 0.67	68 2.68	12.5 0.49	12 0.47

Dimensions in: millimeters / inches

Specification

Sheathing

Thermoplastic polyurethane (TPU)

- Black, matte textured finish
- Elastic, 65 ±5 Shore A
- Operating temperature up to 158 °F (70 °C)
- Abrasion resistant
- Insulating
- Weather-proof

Handle core

- Stainless steel AISI 303, round (for size b = 25 mm)
- Aluminum, elliptical (for size b = 35 mm)

RoHS

On request

- Various metric size fasteners and kit packaging
- Other colors

The shock absorbing thermoplastic polyurethane foam rubber coating of cabinet U-handles GN 564 prevents injuries to the operator, while its elliptical shape gives it a nice hold.

The stainless steel respectively aluminum core guarantees a high basic strength of the handle.

see also...

	Page
GN 565 Cabinet U-Handles (Aluminum)	QVX
EN 725 Cabinet U-Handles (Polypropylene)	QVX

Technical Information

Product Family Softline	QVX
Load Capacity Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 564-25-128

1	Handle width b
2	Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

