




Metric table

Dimensions in: millimeters / inches										
b	¹ l ₁ ±0.25	² a	d ₁	d ₂	h ₁	h ₂	l ₂	l ₃ ≈	r	³ t min.
20 0.79	120 4.72	13 0.51	M 5	5.3 0.21	41 1.61	5 0.20	142 5.59	137 5.39	13 0.51	10 0.39
20 0.79	160 6.30	13 0.51	M 5	5.3 0.21	45 1.77	5 0.20	182 7.17	177 6.97	13 0.51	10 0.39

Specification

Aluminum

- Powder coated
- Black, RAL 9005, textured finish
- Silver, RAL 9006, textured finish
- Anodized finish, natural color
- Plain, tumbled finish

● SW

● SR

● EL

○ BL

RoHS

On request

- Various metric size fasteners and kit packaging

Cabinet U-handles GN 565.3 are manufactured from a bent aluminum profile. They are suitable for applications where lower lifting forces are required such as on lids or protective machine covers.

The countersunk holes of type B allow fixing with self tapping screws or countersunk rivets.

see also...

GN 728 Economical Cabinet U-Handles (Aluminium)

Technical Information

Load Capacity Information

Page

QVX

QVX

www.jwwinco.com | 1-800-877-8351

WARNING: Cancer and Reproductive Harm

— www.P65Warnings.ca.gov

1