



SS Stainless Steel

3 Type

- D With tapped through bore
- E With tapped blind bore

Metric table

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Type D	<sup>2</sup> d <sub>3</sub> Type E	d <sub>4</sub>	h	k	t <sub>1</sub> min.	t <sub>2</sub>
20 0.79	M 5	M 5	11.5 0.45	16 0.63	10 0.39	5 0.20	12 0.47
25 0.98	M 6	M 6	16 0.63	19 0.75	11 0.43	8 0.31	14 0.55
32 1.26	M 8	M 8	17 0.67	22 0.87	13 0.51	10 0.39	16 0.63

Specification

- Plastic  
Technopolymer (Polyamide PA)  
- Reinforced  
- Temperature resistant to 266 °F (130 °C)  
- Black, matte finish
- Tapped insert  
Stainless steel AISI 303
- *Stainless Steel Characteristics* → page QVX
- *Plastic Characteristics* → page QVX
- RoHS compliant

Information

With their stainless steel insert, these EN 590.5 knurled nuts are particularly suited to applications where hygienic, climatic and environmental factors require corrosion resistant materials.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Hollow Knurled Nuts GN 420* → page QVX
- *Knurled Nuts EN 590* → page QVX

How to order <sup>1</sup> <sup>2</sup> <sup>3</sup> <b>EN 590.5-32-M8-E</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub> (Thread d <sub>3</sub> )
	3	Type