


Metric



elesa
Original design I.680 SOFT



Metric table

¹ d ₁ +0.5	² d ₂	d ₃	l ₁	l ₂ min.	l ₃
24 0.94	M 8	20.5 0.81	65 2.56	30 1.18	7 0.28
24 0.94	M 10	20.5 0.81	65 2.56	40 1.57	7 0.28
26 1.02	M 8	21 0.83	80 3.15	40 1.57	7 0.28
26 1.02	M 10	21 0.83	80 3.15	55 2.17	7 0.28
26 1.02	M 12	21 0.83	80 3.15	55 2.17	7 0.28
28 1.10	M 10	22 0.87	90 3.54	56 2.20	7 0.28
28 1.10	M 12	22 0.87	90 3.54	58 2.28	10 0.39

Dimensions in: millimeters / inches

Specification

Base body

Plastic, Polypropylen (PP)

Softline coating

- Thermoplastic elastomer (TPE)
- Chemically bonded with base body
- FDA compliant material
- Operating temperature 32 °F to 176 °F (0 °C to +80 °C)
- Black, matte finish
- Hardness 70 Shore A

RoHS

The Softline coating of cylindrical handles EN 519.6 makes them particularly ergonomic and easy to grip.

The soft, slip-proof contact area improves the grip both in damp (hand perspiration) and in dry ambient conditions, as well as in the event of oily surfaces and in very high or very low temperatures.

see also...

	Page
EN 519 Cylindrical Handles (Plastic)	QVX
EN 519.1 Cylindrical Handles (Press-On Type)	QVX

Technical Information

Product Family Softline	QVX
Plastic Characteristics	QVX

How to order

EN 519.6-26-M10

- ¹ Handle diameter d₁
- ² Thread d₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

