


Metric



elesa

Original design IEL+x SOFT



Metric table

¹ d ₁	² l ₁	³ d ₂		d ₃	d ₄	l ₂	l ₃ ≈
45 1.77	47 1.85	M 10	-	12 0.47	28 1.10	17 0.67	1 0.04
45 1.77	64 2.52	M 8	M 10	12 0.47	21 0.83	17 0.67	1 0.04

Dimensions in: millimeters / inches

Specification

Handle

- Base body
Plastic, Polypropylen (PP)
- Softline coating
Thermoplastic elastomer (TPE)
 - Chemically bonded with base body
 - FDA compliant material
 - Operating temperature from +32 °F to +176 °F (0 °C to +80 °C)
 - Black, matte finish
 - Hardness 70 Shore A

Threaded Spindle

Steel, zinc plated, blue passivated finish

RoHS

Revolving mushroom shaped knobs EN 597.1 are used in applications that require friction-free turning action, such as vertically positioned handwheels or cranked handles.

The Softline coating makes them particularly ergonomic and easy to grip. The **soft, slip-proof** contact area improves the grip both in damp (hand perspiration) and in dry ambient conditions, as well as in the event of oily surfaces and in very high or very low temperatures.

see also...

GN 319.2 Revolving Ball Knobs Page QVX

Technical Information

Product Family Softline QVX

Plastic Characteristics QVX

How to order

EN 597.1-45-47-M10

- ¹ Handle diameter d₁
- ² Length l₁
- ³ Thread d₂

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

