


Inch | Metric



**Inch table**

2 3 Dimensions in: inches / millimeters

d <sub>1</sub>	d <sub>2</sub>		d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
	Plastic	KT					
	KU						
0.71 18	1/4 x 20	1/4 x 20	0.39 10	0.59 15	1.57 40	0.47 12	0.10 2.5
0.83 21	1/4 x 20	1/4 x 20	0.39 10	0.67 17	1.97 50	0.51 13	0.10 2.5
0.91 23	5/16 x 18	5/16 x 18	0.51 13	0.75 19	2.56 65	0.55 14	0.10 2.5
1.02 26	3/8 x 16	3/8 x 16	0.51 13	0.83 21	3.15 80	0.63 16	0.10 2.5
1.10 28	3/8 x 16	3/8 x 16	0.51 13	0.87 22	3.54 90	0.63 16	0.10 2.5
1.22 31	1/2 x 13	-	0.55 14	0.98 25	4.02 102	0.79 20	0.10 2.5

**Metric table**

2 3 Dimensions in: millimeters / inches

d <sub>1</sub>	d <sub>2</sub>		Steel		d <sub>3</sub>	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>
	Plastic	KT	ST						
	KU								
14 0.55	-	M 6	-	-	8 0.31	11 0.43	28 1.10	10 0.39	0.5 0.02
18 0.71	M 6	M 6	M 6	M 6	10 0.39	15 0.59	40 1.57	12 0.47	2.5 0.10
21 0.83	M 6	M 8	M 6	M 8	10 0.39	17 0.67	50 1.97	13 0.51	2.5 0.10
22 0.87	M 6	M 8	M 6	M 8	10 0.39	18 0.71	56 2.20	13 0.51	2.5 0.10
23 0.91	M 8	M 10	M 8	M 10	13 0.51	19 0.75	65 2.56	14 0.55	2.5 0.10
26 1.02	M 8	M 10	M 8	M 10	13 0.51	21 0.83	80 3.15	16 0.63	2.5 0.10
28 1.10	M 10	-	M 10	-	13 0.51	22 0.87	90 3.54	16 0.63	2.5 0.10
31 1.22	M 12	-	-	M 12	14 0.55	25 0.98	102 4.02	20 0.79	2.5 0.10

**Specification**

**Handle**

- Plastic, Phenolic resin (PF) **KU**
  - Operating temperature up to 230 °F (110 °C)
  - Black, shiny finish
- Plastic, Polypropylen (PP) **KT**
  - Operating temperature up to 176 °F (80 °C)
  - Black, matte finish
  - Black, shiny finish (only size 14)
- Steel **ST**
  - Powder coated
  - Black, textured finish

**Threaded Spindle**

Steel, zinc plated, blue passivated finish

RoHS

Revolving handles GN 598 are noted for their modern design, and they blend in well with rectangular shaped rim handwheels.

Steel handles are mainly used on safety clutch handwheels to increase imbalance and thus avoid free wheeling.

**see also...**

	Page
<b>GN 598.1</b> Revolving Handles (Stainless Steel Threaded Spindle)	QVX
<b>EN 539</b> Fixed Cylindrical Handles	QVX
<b>GN 598.3</b> Retractable Handles (with Locking Mechanism)	QVX

**Technical Information**

Plastic Characteristics	QVX
-------------------------	-----

**How to order (Inch)**

1 2 3  
**GN 598-KU-31-1/2X13**

- |   |                                |
|---|--------------------------------|
| 1 | Material                       |
| 2 | Handle diameter d <sub>1</sub> |
| 3 | Thread d <sub>2</sub>          |

**How to order (Metric)**

1 2 3  
**GN 598-KT-21-M8**

- |   |                                |
|---|--------------------------------|
| 1 | Material                       |
| 2 | Handle diameter d <sub>1</sub> |
| 3 | Thread d <sub>2</sub>          |

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

