



Metric



elesa

Original design VRTP-P+I-SST



2 Bore code

- B Without keyway
- K With keyway

4 Type

- R With revolving handle

Metric table

1		3		Dimensions in: millimeters / inches							
d ₁	d ₂ H7	b	d ₃	d ₄	d ₅	l ₁	l ₂	l ₃	r	Ø Handle	
80 3.15	8 0.315	18 0.71	18 0.71	20.5 0.81	25 0.98	17 0.67	35 1.38	45 1.77	29 1.14	16 0.63	
100 3.94	10 0.394	20 0.79	18 0.71	20.5 0.81	25.5 1.00	17 0.67	37 1.46	60 2.36	37 1.46	18 0.71	
125 4.92	12 0.472	22 0.87	22 0.87	26 1.02	31 1.22	22 0.87	44 1.73	65 2.56	48 1.89	22 0.87	
160 6.30	14 0.551	25 0.98	26 1.02	31 1.22	40 1.57	27 1.06	51 2.01	80 3.15	65 2.56	23 0.91	
200 7.87	16 0.630	28 1.10	30 1.18	36 1.42	48.5 1.91	34 1.34	61 2.40	80 3.15	84 3.31	24 0.94	

Specification

Body

- Plastic, Polypropylene (PP)
- FDA compliant plastic granulate
- High strength reinforced, shock-resistant
- Operating temperature +32 °F to +176 °F (0 °C to +80 °C)
- Black, matte finish

Hub bushing

Stainless steel AISI 304
Molded-in

Cover

Stainless steel AISI 304
Self-adhesive

Revolving handle

- Plastic, Polyamide (PA)
- FDA compliant plastic granulate
- Black, matte finish
- Spindle
Stainless steel AISI 304

RoHS

On request

- Other modifications such as special inch and metric bores, set screw holes, etc.

Two spoked handwheels EN 522.5 have an ergonomically shaped rim for a safer and more comfortable grip.

Suitable for use in corrosion free environments. Specifically, the FDA certified plastic materials allow the use in the food industry.

Resistant to solvents, oils, grease and other chemical agents.

Technical Information

	Page
Keyways WN 6885 / DIN 6885-1	QVX
Cross Holes GN 110	QVX
ISO Fundamental Tolerances	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

Accessory

GN 184.5 Countersunk Washers (for Axial Fixing)	QVX
---	-----

How to order

1	Handwheel diameter d ₁
2	Bore code
3	Bore diameter d ₂
4	Type

EN 522.5-125-B12-R