


Metric



SS Stainless Steel

Metric table

1 d_1	2 d_2	3 l_1	d_3	l_2
13 0.51	M 6	9 0.35	8 0.31	18 0.71
14 0.55	M 6	9 0.35	8 0.31	20 0.79
16 0.63	M 6	9 0.35	8 0.31	23 0.91

Dimensions in: millimeters / inches

Specification

Handle

Plastic, Polyamide (PA)

- Operating temperature up to 176 °F (80 °C)
- Black, matte finish

Threaded Spindle

Stainless steel AISI 303

RoHS

Mini cylindrical revolving handles GN 599.5 are mainly used on small handwheels (GN 736, GN 736.1) which are installed for control purposes where low torque is required (fingertip grip).

see also...

	Page
GN 736 Knurled Control Knobs	QVX
GN 736.1 Knurled Control Knobs (with Disposition for Scale)	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 599.5-14-M6-9

1	Handle diameter d_1
2	Thread d_2
3	Length l_1

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

