



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$	<sup>3</sup> Length $l$					$b$	$h$
20 0.79	M 4	6 0.24	10 0.39	-	-	-	9.5 0.37	11 0.43
25 0.98	M 5	10 0.39	16 0.63	25 0.98	-	-	11 0.43	13 0.51
32 1.26	M 6	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	13 0.51	15 0.59
32 1.26	M 8	16 0.63	20 0.79	25 0.98	30 1.18	40 1.57	13 0.51	15 0.59
40 1.57	M 8	16 0.63	25 0.98	40 1.57	-	-	15.5 0.61	17 0.67
48 1.89	M 8	16 0.63	25 0.98	-	-	-	19 0.75	19 0.75
56 2.20	M 10	20 0.79	30 1.18	-	-	-	21 0.83	23 0.91

**Specification**

- Wing body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, matte finish
- Threaded stud  
Stainless steel AISI 303 **NI**
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

Due to their low height EN 531 wing screws offer a comfortable grip for quick two finger clamping applications.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Wing Screws GN 433 (Stainless Steel) → page 678
- Wing Screws GN 431 (Stainless Steel) → page 679

How to order	
<sup>1</sup>	Handle diameter $d_1$
<sup>2</sup>	Thread $d_2$
<sup>3</sup>	Length $l$
<sup>4</sup>	Material

**EN 531-32-M6-30-NI**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4