



Metric



elesa

Original design CTL.476-B / CTL.476-FP

3 Type

- E With tapped blind bore
- D With tapped through bore

Metric table

1

2

Dimensions in: millimeters - inches

d ₁	d ₂ Type E	Type D	d ₃	d ₄	b	h ₁	h ₂	t ₁ min.	t ₂
32 1.26	M 6	M 6	11 0.43	6.5 0.26	13 0.51	14.5 0.57	5.5 0.22	10 0.39	12 0.47
40 1.57	M 8	M 8	14 0.55	9 0.35	15.5 0.61	17 0.67	7.5 0.30	15 0.59	14 0.55
48 1.89	M 8	M 10	17 0.67	11 0.43	19 0.75	19 0.75	9 0.35	20 0.79	16 0.63
56 2.20	M 10	-	18.5 0.73	-	21 0.83	23 0.91	11 0.43	13 0.51	-

Specification

- Wing body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant to 266 °F (130 °C)
- Black, matte finish
- Tapped insert
Brass
- *Plastic Characteristics* → page 2135
- RoHS compliant

Information

EN 532.1 wing nuts offer an extended hub for better surface contact and a comfortable grip for quick two finger clamping applications.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- *Wing Nuts EN 532* → page 665
- *Wing Nuts EN 634* → page 660
- *Small Wing Nuts EN 640* → www.jwwinco.com

How to order

EN 532.1-48-M8-E

- 1 Handle diameter d₁
- 2 Thread d₂
- 3 Type