



Inch table

Dimensions in: inches - millimeters

¹ l ₁	² d ₁			d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
1.18 30.0	10 x 24	10 x 32	1/4 x 20	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6	0.39 9.9
1.73 43.9	10 x 24	10 x 32	1/4 x 20	0.47 11.9	0.61 15.5	1.16 29.5	0.24 6.1	1.06 26.9	0.14 3.6	0.39 9.9
2.48 63.0	1/4 x 20	5/16 x 18	-	0.59 15.0	0.75 19.1	1.48 37.6	0.31 7.9	1.44 36.6	0.14 3.6	0.63 16.0
3.07 78.0	5/16 x 18	3/8 x 16	1/2 x 13	0.75 19.1	0.96 24.4	1.85 47.0	0.41 10.5	1.69 43.0	0.14 3.6	0.79 20.1

Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁			d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	t min.	
30 1.18	M 3	M 4	M 5	M 6	12 0.47	15.5 0.61	29.5 1.16	6 0.24	27 1.06	3.5 0.14	10 0.39
44 1.73	M 5	M 6	-	-	12 0.47	15.5 0.61	29.5 1.16	6 0.24	27 1.06	3.5 0.14	10 0.39
63 2.48	M 6	M 8	-	-	15 0.59	19 0.75	37.5 1.48	8 0.31	36.5 1.44	3.5 0.14	16 0.63
78 3.07	M 8	M 10	M 12	-	19 0.75	24.5 0.96	47 1.85	10.5 0.41	43 1.69	3.5 0.14	20 0.79

Specification

- Lever body / serrated insert
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 265 °F (130 °C)
- Black-gray, similar to RAL 7021, matte finish
- Color of the push button (shiny finish):
 - DSG
 - DOR
 - DGR
 - DGB
 - DBL
 - DRT
 - DGN
- Tapped insert
Brass, molded-in
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 600 straight adjustable levers are renowned for their style and ergonomic shape. Like all adjustable levers, they are ideal whenever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged. Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage. Resistant to solvents, oils, grease and other chemical agents.

see also...

- Product Family Ergostyle® → page QVX
- Adjustable Levers EN 603 (with Push Button) → page QVX

On request

- With stainless steel tapped insert

How to order	1	2	3
¹ Lever length l ₁			
² Thread d ₁			
³ Color of the push button			

EN 600-1.18-10X24-DSG