



Metric table

Dimensions in: millimeters - inches

1	2	2	2	3										
l_1	d_1 Thread	d_2 H9 Bore	s H9 Square	l_2		d_3	d_4	d_5	e	h_1	h_2	h_3	t_1 min.	t_2 min.
44 1.73	M 5	-	-	-	-	15.5 0.61	-	-	-	19 0.75	26.5 1.04	19 0.75	12 0.47	-
44 1.73	M 6	B 6	V 5	16 0.63	-	15.5 0.61	3 0.12	M 4	7 0.28	19 0.75	26.5 1.04	19 0.75	12 0.47	15 0.59
63 2.48	M 8	B 8	V 6	25 0.98	45 1.77	19 0.75	4 0.16	M 4	8 0.31	24.5 0.96	35 1.38	26.5 1.04	13 0.51	20 0.79
78 3.07	M 10	B 10	V 8	30 1.18	-	23 0.91	4 0.16	M 5	9 0.35	29.5 1.16	42 1.65	32 1.26	17 0.67	25 0.98
95 3.74	M 12	B 12	V 10	50 1.97	-	26.5 1.04	5 0.20	M 5	10 0.39	34 1.34	51.5 2.03	40 1.57	20 0.79	30 1.18

Specification

- Lever body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish
- Tapped insert
Brass
- Threaded stud
Steel, zinc plated, blue passivated finish
- Set screw DIN 916
Steel, blackened finish
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 601 clamping levers are the result of modern industrial design. The tapped insert / threaded stud insert is molded into the lever.

see also...

- Product Family Ergostyle® → page QVX

<p>How to order (With bore)</p> <p>1 2</p> <p>EN 601-44-V5</p>	1	Lever length l_1
	2	Square s (Thread d_1 , Bore d_2)
<p>How to order (With threaded stud)</p> <p>1 2 3</p> <p>EN 601-63-M8-25</p>	1	Lever length l_1
	2	Thread d_1
	3	Thread length l_2