



Metric table

Dimensions in: millimeters - inches

| ¹ d ₁ | ² s H9 Square | | d ₂ | d ₃ | h ₁ | h ₂ | t |
|-----------------------------|--------------------------|-----|----------------|----------------|----------------|----------------|-----------|
| 40 1.57 | V 6 | - | 14 0.55 | 21 0.83 | 15 0.59 | 10 0.39 | 4 0.16 |
| 50 1.97 | V 6 | V 7 | 14 0.55 | 24 0.94 | 18 0.71 | 10 0.39 | 5 0.20 |
| 60 2.36 | V 6 | V 7 | 16 0.63 | 29 1.14 | 20 0.79 | 10 0.39 | 4 0.16 |
| 70 2.76 | V 7 | V 8 | 18 0.71 | 35 1.38 | 22 0.87 | 14 0.55 | 5 0.20 |
| 85 3.35 | V 8 | V 9 | 18 0.71 | 45 1.77 | 25 0.98 | 14 0.55 | 8 0.31 |
| 100 3.94 | V 10 | - | 18 0.71 | 57 2.24 | 28 1.10 | 14 0.55 | 6 0.24 |

Specification

- Five-lobed knob
Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Square bushing
Brass
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 5333 five-lobed knobs meet highest quality requirements. Due to a special manufacturing process a mold parting line is eliminated.
Resistant to solvents, oils, grease and other chemical agents.

| | |
|--|---|
| How to order ¹ ² EN5333-50-V7 | 1 Handle diameter d ₁ |
| | 2 Square s |