



Inch table

Dimensions in: inches - millimeters

¹ l ₁	² d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	t min.
1.73 44	1/4 x 20	0.47 12	0.61 15.5	1.14 29	0.35 9	1.42 36	0.14 3.5	0.39 10
2.48 63	5/16 x 18	0.59 15	0.75 19	1.46 37	0.47 12	1.89 48	0.16 4	0.51 13

Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄ Stroke	t min.		
44 1.73	M 4	M 5	M 6	12 0.47	15.5 0.61	29 1.14	9 0.35	36 1.42	3.5 0.14	10 0.39
63 2.48	M 6	M 8	-	15 0.59	19 0.75	37 1.46	12 0.47	48 1.89	4 0.16	13 0.51

Specification

- Lever body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black-gray, RAL 7021, matte finish ● SG
- Tapped insert / retaining screw
Steel, blackened finish
- Plastic Characteristics → page 2135
- RoHS compliant

Information

EN 604.2 safety adjustable levers like all the products of the Ergostyle® product family are renowned for their good style and also their ergonomic shape. The gently arched handle with a reinforced end of the lever gives the operator a good grip.

These safety adjustable levers are used where the inadvertent loosening or readjustment can result in accidents.

If not operated, the lever is not linked to the tapped insert, i.e. the adjustable lever turns freely.

As soon as the lever hub is pushed down, both serrations will engage, allowing the fixture to be released or clamped.

After “releasing”, the connection disengages through spring tension.

see also...

- Product Family Ergostyle® → page 18
- Safety Adjustable Levers GN 312 → page 536
- Safety Lobed Knobs GN 5337.3 → page 613

How to order (Inch)	1 Lever length l ₁
¹ ² ³ EN 604.2-44-1/4X20-SG	2 Thread d ₁
	3 Color

How to order (Metric)	1 Lever length l ₁
¹ ² ³ EN 604.2-63-M8-SG	2 Thread d ₁
	3 Color