



SS Stainless Steel

3 Type

- E With tapped blind bore
- C With plain blind bore, tol. H7

Inch table

1 d ₁	2 d ₂ GN 5334 Thread	d ₄	h ₁ ≈	h ₂ ≈	t min.
1.57 40	5/16 x 18	0.55 14	0.94 24	0.47 12	0.59 15
1.97 50	3/8 x 16	0.71 18	1.18 30	0.65 16.5	0.71 18
2.36 60	1/2 x 13	0.79 20	1.48 37.5	0.79 20	0.87 22

Dimensions in: inches - millimeters

Metric table

1 d ₁	2 d ₂ GN 5334 / GN 5334.4 Thread		2 d ₃ H7 GN 5334 / GN 5334.4 Bore	d ₄	h ₁ ≈	h ₂ ≈	t min.
32 1.26	M 5	M 6	B 6	12 0.47	21 0.83	10 0.39	12 0.47
40 1.57	M 6	M 8	B 8	14 0.55	24 0.94	12 0.47	15 0.59
50 1.97	M 8	M 10	B 10	18 0.71	30 1.18	16.5 0.65	18 0.71
60 2.36	M 10	M 12	B 12	20 0.79	37.5 1.48	20 0.79	22 0.87

Dimensions in: millimeters - inches

Specification

- **GN 5334**
Stainless steel AISI 304
- **GN 5334.4**
Stainless steel AISI 316L

This information applies to both series:

- Knob drawn from stainless steel sheet
- Hub welded
- Matte shot-blasted finish
- *Cross Holes GN 110* → page 2042
- *ISO Fundamental Tolerances* → page 2129
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Special inch and metric bores or threads
- Other modifications such as cross holes and set screw holes

Information

The original ELESA design with 5 recess grips is typical for star knobs GN 5334 / GN 5334.4. This form gives these grips an appealing look and additionally allows a high torque to be achieved. Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

see also...

- *Triangular Knobs GN 5339.5 (Stainless Steel)* → page 656
- *Star Knobs GN 5335 (Stainless Steel)* → page 620
- *Wing Nuts GN 834 (Stainless Steel)* → page 676
- *Star Knobs DIN 6336 (Stainless Steel)* → page 572
- *Hand Knobs DIN 6335 (Stainless Steel)* → page 626
- *Three-Lobed Knobs GN 5345 (Stainless Steel)* → page 640
- *Star Knobs GN 5334 with Loss Protection GN 111.7 (Stainless Steel)* → page 2046

How to order (Inch, stainless steel AISI 304) GN 5334-40-5/16X18-E	1 Handle diameter d ₁
	2 Thread d ₂
	3 Type
How to order (Metric, stainless steel AISI 316L) GN 5334.4-40-B8-C	1 Handle diameter d ₁
	2 Bore d ₃ (Thread d ₂)
	3 Type